

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST
J	-

REVISIONS 変更

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED	07OCT2009	M.M	T.K






AS SHOWN : 2069524-1(W)

1. GENERAL TOLERANCES: SEE FOLLOWS
   0.00- 9.00 : ±0.3
   10.00-19.00 : ±0.4
   20.00-29.00 : ±0.5
   30.00- : ±0.6
   ANGLES : ±5°


2. MATERIAL: GLASS FILED THERMO PLASTIC POLYESTER(94V-0), COLOR: BLACK

3. THE SHAPE, SIZE AND POSITION OF THE CHARACTER SHOW THE OUTLINE. THEY DON'T SHOW DETAILS.


KEYING LAYOUT



2069524-2(X)



2069524-3(Y)



2069524-4(Z)

Z	2069524-4
Y	2069524-3
X	2069524-2
W	2069524-1
KEY	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS: 単位: 粍 mm

TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差
0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

MATERIAL 材料 2

FINISH 仕上

DWN 07OCT2009 M.MAEBASHI
CHK 07OCT2009 N.YAMASAKI
APVD 07OCT2009 T.KIMURA
PRODUCT SPEC 製品規格 108-78644
APPLICATION SPEC 取付適用規格 -
WEIGHT 38.0

Tyco Electronics
Tyco Electronics Corporation
Kawasaki, Japan

NAME 名称
DYNAMIC HIGH DENSITY FRAME
PLUG FRAME HOUSING
4 MODULES

SIZE	CAGE CODE	DRAWING NO 番号	RESTRICTED TO
A3	00779	C-2069524	-

CUSTOMER DRAWING | SCALE 尺度 1:1 | SHEET 1 OF 1 | REV A

AMP 1470-19 REV 31MAR2000

Downloaded from Arrow.com.