

Power Extension Cord, NEMA L5-30P to NEMA L5-30R- Heavy-Duty, 30A, 125V, 10 AWG, 10 ft. (3.05 m), Black, Locking Connectors

MODEL NUMBER: P046-010-LL-30A



Heavy-duty extension cord connects your computer or other device with a NEMA L5-30P plug to a NEMA L5-30R outlet.

Features

Heavy-Duty Extension Cable for Network Devices That Require a Heavy-Gauge Connection This cord features 10 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. It can be used to connect a computer, server or other device with a NEMA L5-30P plug to a wall outlet, PDU or UPS system with a NEMA L5-30R outlet. The six-foot length allows you flexibility in placing equipment with respect to the power outlet.

Locking Connectors Help Prevent Accidental Disconnection and Expensive Downtime Having a cable come loose accidentally can mean the loss of power and costly downtime. Locking connectors on each end help you avoid such danger, protecting critical equipment by maintaining a secure link without failure. The locking cable is also invaluable when moving equipment in a rack or removing equipment from tight areas, ensuring the power cord always stays connected.

Specifications

OVERVIEW	
UPC Code	037332200945
Device Compatibility	UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	30
Voltage Compatibility (VAC)	125

Highlights

- Recommended for powering computers, servers and other network devices
- 10-ft. (3.05 m) length allows flexibility in placing devices in relationship to AC outlet
- Heavy-duty cord replaces or upgrades standard power cord provided by manufacturer
- Thick 10 AWG wire gauge manages high power levels required for larger equipment
- Locking connectors maintain secure link to avoid loss of power and costly downtime

Applications

- Connect devices like computers, servers and monitors to a PDU in your data center
- Extend an existing power connection up to 10 ft. to more easily place a device or reach a power source in a rack
- Update or replace the standard power cord provided by a device's original manufacturer

Package Includes

- P046-006-LL-30A L5-30P to L5-30R Heavy-Duty Extension Cord, 10 ft., Black, Locking Connectors



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Power Cord Jacket Type	SJT
Number of Conductors	3
Wire Gauge (AWG)	10
Wire Gauge (OD - mm ²)	5.26
Cable Length (ft.)	10
Cable Length (m)	3.05
Cable Length (cm)	304.80
Shipping Dimensions (hwd / cm)	1.27 x 25.40 x 37.34
Shipping Dimensions (hwd / in.)	0.50 x 10.00 x 14.70
Shipping Weight (kg)	1.18
Shipping Weight (lbs.)	2.60
ENVIRONMENTAL	
Operating Temperature Range	41 F TO 95 F (5 C TO 35 C)
Storage Temperature Range	41 F TO 95 F (5 C TO 35 C)
Operating Humidity Range	0-65% RH
Storage Humidity Range	0-65% RH
CONNECTIONS	
Side A - Connector 1	NEMA L5-30P
Side B - Connector 1	NEMA L5-30R
FEATURES & SPECIFICATIONS	
High Voltage	No
Locking Plug	Yes
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>