

USB 2.0 All-in-One Keystone/Panel Mount Coupler (F/F), White

MODEL NUMBER: **U060-000-KP-WH**



USB 2.0 keystone coupler snaps into a wall plate or panel cutout to connect 2 USB-A cables and complete an in-wall run. Optional panel mount adapter included for installation in a motherboard, podium or kiosk.

Description

The U060-000-KP-WH USB 2.0 All-in-One Keystone/Panel Mount Coupler (F/F) is recommended for completing an in-wall USB cable run, connecting two USB devices or extending the length of an existing USB application. It also can give your conference room, classroom, home theater room or retail establishment a professional, tidy look by hiding components out of sight in a closet or another room to eliminate cable clutter.

The keystone design snaps easily into the cutout of a wall plate or panel. An optional panel mount adapter is included for securing the coupler to a motherboard, podium or kiosk. Compatible with all USB-A cables, the U060-000-KP-WH features molded nickel-plated connectors with gold-plated contacts for maximum conductivity and minimum data loss. The heavy-duty white plastic housing is designed for durability and long life.

Features

Connects 2 USB-A Cables to Create a Longer Cable Run

- Keystone design snaps easily into wall plate or panel
- Hides components out of sight to eliminate cable clutter
- Optional panel mount adapter allows installation in motherboard, podium or kiosk

Premium Construction for Superior Signal Transfer

- Molded connectors with gold-plated contacts provide maximum conductivity and minimize data loss
- Heavy-duty plastic housing designed for durability and long life

Highlights

- Hides components out of sight to eliminate cable clutter
- Gold-plated contacts for max conductivity and minimum data loss
- Optional panel mount adapter secures to podium or kiosk
- Keystone design snaps easily into standard wall plate or panel
- White in color to match most common wall plates

Package Includes

- U060-000-KP-WH USB All-in-One Keystone/Panel Mount Coupler (F/F), White



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- White in color to match most common wall plates

Specifications

OVERVIEW	
UPC Code	037332209894
PHYSICAL	
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.03
Shipping Weight (kg)	0.01
Material of Construction	ABS
Color	White
ENVIRONMENTAL	
Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	-4 to 140 F (-20 to 60 C)
Relative Humidity	10% to 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	USB A (FEMALE)
Side B - Connector 1	USB A (FEMALE)
Connector Plating	Nickel
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
Technology	USB; USB 2.0 (High Speed)
CERTIFICATIONS	
Certifications	ROHS Compliant, CE
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>