

[Relays, Contactors & Switches](#) > [Relays](#) > [Mil-Aero Relays](#) > [TO-5/.100 Grid](#)

PRMAW-12X=COTS TO-5 RELAY



✓ **ACTIVE**

CII

TE Part # **PRMAW-12X**
TE Internal #: **2-1617778-8**

Contact Arrangement : **2 Form C, DPDT, 2 C/O**

Input Voltage (VDC): **7**

Coil Suppression Diode : **Without**

MOSFET Driver : **Without**

Transistor Driver : **Without**

 [Add to List](#) > [Similar Products](#)

Compatible Parts & Tooling

SHOP OUR DISTRIBUTORS

North America ▼

Request pricing, availability and customization options

CONTACT US



We are here to help!

Get in touch with our product experts.



CHAT WITH US



EMAIL US



CALL US

DOCUMENTS

FEATURES

PRODUCT COMPLIANCE

Catalog
Pages/Data
Sheets

 [ENG_DS_PRMAW-12X_A.pdf](#) English

Please review product documents or [contact us](#) for the latest agency approval information.

Product Type
Features

MOSFET Driver : **Without**

Product Type : **Relay**

Coil Latching : **Without**

Relay Type : **Military/Aerospace High Performance**

Enclosure Type : **Hermetically Sealed**

Configuration
Features

Transistor Driver : **Without**

Electrical
Characteristics

Coil Power Measurement :
Milliwatts

Input Voltage (VDC): **7**

Coil Suppression Diode : **Without**

	Coil Voltage (VDC): 12 Coil Resistance (Ω): 390 Coil Power Rating (DC) (mW): 369 Coil Polarity Protection Diode : Without Contact Switching Voltage (Max) : 28 Shock : 75G's, 6ms Actuating System : DC Vibration : 30G's, 10 – 3000Hz Coil Magnetic System : Non-Polarized, Monostable
Contact Features	Contact Arrangement : 2 Form C, DPDT, 2 C/O Contact Current Rating (A): 1 Contact Current Class : Low Level – 1 A
Termination Features	Termination Type : Long Leads
Mechanical Attachment	Mounting Type : Printed Circuit Board
Usage Conditions	Operating Temperature Range (°C): -65 – 125
Statement of Compliance	Statement of Compliance pdf


Compatible Parts

> [Contact Product Support](#)


Customers Also Bought



TE Part # 211676-4
**HD90 62 POS GRMT
ASY PLUG HSG**



TE Part # 446852-1
**3 ROW BOX PIN 90P
R/A SEALED**



TE Part # 446853-1
**3 ROW BOX REC 90P
100CL SEALED**



TE Part # DL64H-20-41PN-805
HERM RECP

