


A-INB-M12-69KN-S-S - Pressure compensation element



1415224
<https://www.phoenixcontact.com/us/products/1415224>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



Pressure compensation element, material for screw connection: Stainless steel 1.4305, connecting thread: M12 x 1.5, color: silver, with O-ring

Your advantages

- Reduces the formation of condensation

Commercial Data

Item number	1415224
Packing unit	1 pc
Minimum order quantity	5 pc
Sales Key	BF68
Product Key	BF7DZX
Catalog Page	Page 695 (C-2-2019)
GTIN	4055626038674
Weight per Piece (including packing)	15.81 g
Weight per Piece (excluding packing)	15.81 g
Customs tariff number	73269098
Country of origin	TR

A-INB-M12-69KN-S-S - Pressure compensation element




1415224
<https://www.phoenixcontact.com/us/products/1415224>

Technical Data

Product properties

Product type	Pressure compensation element
--------------	-------------------------------

Dimensions

Dimensional drawing	
Length	21 mm
Length of the connecting thread	10 mm
Length without connecting thread	11 mm
Diameter	12 mm
Connecting thread diameter	12 mm
Wrench size, union nut	17 mm
Hexagon angular dimension	18.5 mm
Thread type connection side	M12 x 1.5
Thread pitch	1.5 mm

Material specifications

Color	silver
Material	Acrylic copolymer
	Stainless steel 1.4305
Seal material	Perbunan
Material for screw connection	Stainless steel 1.4305

Characteristics

Tightening torque	0.5 Nm ... 1 Nm (Flange)
-------------------	--------------------------

Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP66
	IP67
	IP69
Ambient temperature (operation)	-40 °C ... 105 °C

A-INB-M12-69KN-S-S - Pressure compensation element




1415224

<https://www.phoenixcontact.com/us/products/1415224>

Drawings

Dimensional drawing



A-INB-M12-69KN-S-S - Pressure compensation element



1415224
<https://www.phoenixcontact.com/us/products/1415224>

Classifications

ECLASS

ECLASS-9.0	27440192
ECLASS-10.0.1	27440192
ECLASS-11.0	27440192
ECLASS-12.0	27440192
ECLASS-13.0	27440192

ETIM

ETIM 8.0	EC002943
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

A-INB-M12-69KN-S-S - Pressure compensation element



1415224
<https://www.phoenixcontact.com/us/products/1415224>

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

A-INB-M12-69KN-S-S - Pressure compensation element



1415224

<https://www.phoenixcontact.com/us/products/1415224>

Accessories

A-INL-M12-S-S - Counter nut

1425175

<https://www.phoenixcontact.com/us/products/1425175>

Counter nut, for threads M12 x 1.5, color: silver



Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com