

[Printer Labels](#) / [Bradyprinter PR Plus Printer Labels](#) /

3" Core Series MetaLabel Gloss Metallized Polyester Labels

3" Core Series MetaLabel Gloss Metallized Polyester Labels



Product Highlights:

Label/Tape Size:

0.75 in H x 1.5 in W

Material:

Metallized Polyester

For Use with Printer:

BBP®81 Label Printer, BRADY IP® Series
Label Printer, BradyPrinter i5100,
BradyPrinter i7100, BRADYPRINTER PR
Plus Series Label Printer, THT 3" Core
Printer

Material Number:

B-434

Color:

Silver

Quantity per Roll:

10000

Part Number:

THT-6-434-10

ADD TO CART

1



Add To Favorites

Need a different size? Customize it!

PEOPLE ALSO VIEWED

OVERVIEW

Metallized Polyester (B-434) labels are designed for applications that use barcodes, alphanumerics, graphic symbols and logos and require nameplate-like quality.

- Glossy, light gray finish gives labels a rating and serial plate appearance
- Labels are designed to withstand numerous solvents and variable temperatures when applied to various surfaces

- RoHS compliant to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC; UL approved; CSA accepted
- Service temperature of -40 to 194° F (-40 to 90° C)

SPECIFICATIONS

Material Number	B-434
Catalog Page #	165
Dimensions	0.75 in H x 1.5 in W
UOM	Roll of 10000 Labels
Finish	Gloss
Label/Tape Size	0.75 in H x 1.5 in W
Maximum Service Temperature °F	194 °F
Minimum Service Temperature °F	-40 °F
Printable Area Dimensions	0.75 in H x 1.5 in W
Printable Area Height	0.75 in
Printable Area Width	1.5 in
Product Number	30281
UPC	662820302810
Quantity per Roll	10000
Quantity per Row	2
Secondary Label Included	Secondary Label is Not Included
Thickness	0.004 in
Trade Name	MetaLabel™
Unit Price	/Label
Adhesive Type	Acrylic
Applications	Asset Tracking, General & Industrial ID, Rating Plates
Color	Silver
For Use with Printer	BBP®81 Label Printer, BRADY IP® Series Label Printer, BradyPrinter i5100, BradyPrinter i7100, BRADYPRINTER PR Plus Series Label Printer, THT 3" Core Printer
Label/Media Format	Roll
Label Properties	Metallic Labels, Permanent Adhesive Labels
Material	Metallized Polyester
Material Properties	Metallic Appearance

Print Technology	Thermal Transfer
Resistance Properties	Abrasion-Resistant, Humidity-Resistant, UV-Resistant, Weather-Resistant
Shape	Rectangle
Suggested Ribbon Series	R4800, R4900, R6000, R6200

Solutions

[Floor Marking Guide](#)
[GHS Label Compliance](#)
[Lockout Tagout Compliance](#)
[Arc Flash Labeling Requirements](#)
[Cable and Wire Label Options](#)
[Product and Barcode Labeling](#)
[Brand Protection Solutions](#)

Services

[Lockout Tagout Services](#)
[Arc Flash Services](#)
[Confined Space Services](#)
[Software Programming & Integration](#)
[Label Template & File Conversion](#)
[Printer Use & Training](#)
[Printer Preventative Maintenance](#)
[Toll and Custom Coating](#)
[Authentication & Tracking Services](#)

Help

[Contact Us](#)
[Website Feedback](#)
[Knowledge Center](#)
[Printer Drivers & Firmware](#)
[Brady Software Updates](#)
[Safety Data Sheets](#)
[Technical Data Sheets](#)
[WEEE-RoHS Compliance](#)
[Product Certification](#)
[Printer Registration](#)

Resources

[Find a Distributor](#)
[Design Custom Safety Signs](#)
[Printer Selection Tool](#)
[Label Selection Tool](#)
[Digital Catalog](#)
[Request a Catalog](#)
[Interactive Facility Map](#)
[EPA e-Manifest Update](#)

Corporate


[About](#)
[Careers](#)
[Investors](#)
[Privacy Policy](#)
[Terms and Conditions](#)
[Terms of Use](#)
[ISO Certificates](#)

Other BradyContact Sites

[Distributor Portal](#)
[International Sites](#)
[Safety Services & Software](#)
[Smart ID Brand Protection Solutions](#)

6555 W. Good Hope Rd.
 Milwaukee, WI 53223
 Phone: 888-250-3082
 Hours: 7am-6pm CT
 Monday - Thursday;
 Friday 7am-5pm CT

Brady (NYSE:BRC) is a manufacturer of complete solutions that identify and protect people, products and places. Brady's products help customers increase safety, security, productivity and performance and include high-performance labels, signs, safety devices, printing systems and software.



2018 © Brady Worldwide, Inc.