

NS 15 WH PERF 2000MM-VPE 10 - DIN rail perforated



1204096

<https://www.phoenixcontact.com/us/products/1204096>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail perforated, Pack of 10 (20 m), acc. to EN 60715, material: Steel, galvanized, white passivated, Standard profile, color: silver-colored

Commercial data

Item number	1204096
Packing unit	10 m
Minimum order quantity	20 m
Sales key	BE72
Product key	BE7223
GTIN	4017918106430
Weight per piece (including packing)	308 g
Weight per piece (excluding packing)	308 g
Customs tariff number	72166190
Country of origin	DE

NS 15 WH PERF 2000MM-VPE 10 - DIN rail perforated



1204096


<https://www.phoenixcontact.com/us/products/1204096>

Technical data

Product properties

Product type	DIN rail
--------------	----------

Dimensions

Dimensional drawing	
Width	15 mm
Hole width	12.2 mm
Hole height	4.2 mm
Depth	5.5 mm
Length	2000 mm
Drill hole spacing	20 mm

Material specifications

Color	silver-colored
Material	Steel
Coating	galvanized, white passivated

Standards and regulations

Connection in acc. with standard	IEC / EN
Tests	acc. to EN 60715

NS 15 WH PERF 2000MM-VPE 10 - DIN rail perforated




1204096

<https://www.phoenixcontact.com/us/products/1204096>

Drawings

Dimensional drawing



NS 15 WH PERF 2000MM-VPE 10 - DIN rail perforated



1204096

<https://www.phoenixcontact.com/us/products/1204096>

Classifications

ECLASS

ECLASS-13.0	27400602
ECLASS-15.0	27400602

ETIM

ETIM 9.0	EC001285
----------	----------

UNSPSC

UNSPSC 21.0	39121700
-------------	----------

NS 15 WH PERF 2000MM-VPE 10 - DIN rail perforated



1204096

<https://www.phoenixcontact.com/us/products/1204096>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com