



Part Number : 194130110
Product Description : Solderless Terminals Kit, Non-Insulated Terminals, 180 Pieces
Series Number : 19413
Status : Active
Product Category : Kits
Engineering Number : KIT-MX15



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Kits
Series	19413
Description	Solderless Terminals Kit, Non-Insulated Terminals, 180 Pieces
Comments	Includes 15 of each part number in the kit. See Kit Components below for links to included parts.
Component Type	Kit
Kit Component Parts	VersaKrimp Ring Tongue Terminal for 12-10 AWG Wire, Closed-Brazed Barrel, Stud Size 8 (M4), Carton, VersaKrimp Ring Tongue Terminal for 12-10 AWG Wire, Closed-Brazed Barrel, Stud Size 10 (M5), Carton, VersaKrimp Ring Tongue Terminal for 12-10 AWG Wire, Closed-Brazed Barrel, Stud Size 1/4" (M6), Carton, VersaKrimp Ring Tongue Terminal for 12-10 AWG Wire, Closed-Brazed Barrel, Stud Size 3/8" (M9), Carton, VersaKrimp Ring Tongue Terminal for 16-14 AWG Wire, Non-Insulated, Stud Size 6, VersaKrimp Ring Tongue Terminal for 16-14 AWG Wire, Non-Insulated, Stud Size 8, VersaKrimp Ring Tongue Terminal for 16-14 AWG Wire, Non-Insulated, Stud Size 10, VersaKrimp Ring Tongue Terminal for 16-14 AWG Wire, Non-Insulated, Stud Size 0.25", VersaKrimp Ring Tongue Terminal for 22-18 AWG Wire, Non-Insulated, Stud Size 6, VersaKrimp Ring Tongue Terminal for 22-18 AWG Wire, Non-Insulated, Stud Size 8, VersaKrimp Ring Tongue Terminal for 22-18 AWG Wire, Non-Insulated, Stud Size 10, VersaKrimp Ring Tongue Terminal for 22-18 AWG Wire, Non-Insulated, Stud Size

	0.25"
Product Name	Solderless Terminals Kit
UPC	191128415378

Physical

Circuits (Loaded)	N/A
Depth	32.00mm
Length	210.00mm
Width	114.00mm

Kit Component Parts

Description	Part Number
VersaKrimp Ring Tongue Terminal for 12-10 AWG Wire, Closed-Brazed Barrel, Stud Size 8 (M4), Carton	<u>191930106</u>
VersaKrimp Ring Tongue Terminal for 12-10 AWG Wire, Closed-Brazed Barrel, Stud Size 10 (M5), Carton	<u>191930109</u>
VersaKrimp Ring Tongue Terminal for 12-10 AWG Wire, Closed-Brazed Barrel, Stud Size 1/4" (M6), Carton	<u>191930116</u>
VersaKrimp Ring Tongue Terminal for 12-10 AWG Wire, Closed-Brazed Barrel, Stud Size 3/8" (M9), Carton	<u>191930137</u>
VersaKrimp Ring Tongue Terminal for 16-14 AWG Wire, Non-Insulated, Stud Size 6	<u>190560065</u>
VersaKrimp Ring Tongue Terminal for 16-14 AWG Wire, Non-Insulated, Stud Size 8	<u>190560106</u>
VersaKrimp Ring Tongue Terminal for 16-14 AWG Wire, Non-Insulated, Stud Size 10	<u>190560109</u>
VersaKrimp Ring Tongue Terminal for 16-14 AWG Wire, Non-Insulated, Stud Size 0.25"	<u>190560072</u>
VersaKrimp Ring Tongue Terminal for 22-18 AWG Wire, Non-Insulated,	<u>190560010</u>

Stud Size 6	
VersaKrimp Ring Tongue Terminal for 22-18 AWG Wire, Non-Insulated, Stud Size 8	<u>190560015</u>
VersaKrimp Ring Tongue Terminal for 22-18 AWG Wire, Non-Insulated, Stud Size 10	<u>190560018</u>
VersaKrimp Ring Tongue Terminal for 22-18 AWG Wire, Non-Insulated, Stud Size 0.25"	<u>190560023</u>

This document was generated on Sep 10, 2025