




WAGO-I/O-CHECK is an easy-to-use Windows application for operating and displaying a WAGO I/O System 750's node without connecting to a fieldbus system. The software reads the configuration from the node and displays it graphically on the screen. This graphic can be printed together with a configuration list as documentation. With WAGO-I/O-CHECK, it is possible to display and specify the process data of the I/O modules. The field wiring, including all sensors and actuators, can thus be checked before startup. For some types of interface, Pt100 and thermocouple modules, application-specific settings can be made, such as the baud rate or sensor types. The coupler must be connected to a free serial or USB port of the PC using the communication cable supplied in the set with the system to enable communication between WAGO-I/O-CHECK and the node.

System requirements	
Supported operating systems	Windows 7 Windows 10
Processor	1 GHz or higher, with 32 bits (x86) or 64 bits (x64)
Memory	Min. 1 GB RAM 2 GB RAM or more (recommended)
Hard disk space	min. 150 MB
Graphics resolution	1024 x 786 (min.), 1280 x 1024 or higher (recommended)

Delivery	
Delivery type	Installation file (CD-ROM)
Scope of delivery	CD-ROM with software and serial communication cable (750-920)

Commercial data	
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	DE
GTIN	4045454394899
Customs tariff number	85234920009



Product Classification	
ETIM 10.0	EC001435
UNSPSC	43232605
eCl@ss 10.0	27-24-25-90
eCl@ss 9.0	27-24-25-90
ETIM 9.0	EC001435
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant,No Exemption

Downloads	
Environmental Product Compliance	
Compliance Search	
Environmental Product Compliance 759-302	↓

Documentation			
Manual		System Description	
Product Manual WAGO-I/O-CHECK Commissioning Tool for WAGO-I/O-SYSTEM 750	V 1.2.0	pdf	1158.70 KB
		↓	
		pdf	368.80 KB
		↓	

Bid Text			
759-302	19.02.2019	xml	4.80 KB
		↓	
759-302	10.01.2019	docx	16.26 KB
		↓	

Application Notes			
Application Note e!COCKPIT			
e!COCKPIT application note WagoSolElsner	1.0.2 06.12.2021	pdf	512.20 KB
		↓	



1 Compatible Products
1.1 Optional Accessories
1.1.1 Communication
1.1.1.1 Communication cable



Item No.: 750-920 Communication cable	Item No.: 750-923 Configuration cable; USB connector; Length: 2.5 m	Item No.: 750-923/000-001 Configuration cable; USB connector; Length: 5 m
--	---	---