











奇数キャビティ：キャビティ番号及び金型番号
偶数キャビティ：トレードマーク
ODD CAV:CAVITY & MOLD NUMBER
EVEN CAV:TRADE MARK



奇数キャビティ：トレードマーク
偶数キャビティ：キャビティ番号及び金型番号
ODD CAV:TRADE MARK
EVEN CAV:CAVITY & MOLD NUMBER







ターミナル装着図
TERMINAL ASSEMBLY DRAWING

注記：
NOTES :

1. 材質：TABLE 1参照
   MATERIAL : SEE TABLE 1.
2. 偶数極に適用。
   APPLY TO EVEN CIRCUIT.
3. 製品仕様書、コネクタ取扱説明書、適合嵌合相手、適合ターミナルはSHEET 3をご参照ください。
   PLEASE REFER TO SHEET 3 FOR PRODUCT SPECIFICATION, APPLICATION SPECIFICATION, MATE WITH AND APPLICABLE TERMINAL.
4. 発注番号 : SHEET 3 参照
   ORDER NUMBER : PLEASE REFER TO SHEET 3

204532**0*

極数 CIRCUIT SIZE

番号 NO.	ハウジングカラー HOUSING COLOR
0	ナチュラル (白) NATURAL (WHITE)
1	黒 BLACK

1 TABLE 1

部品 PART	材質 MATERIAL
ハウジング HOUSING	ポリエステル(PBT), UL94 V-0, 色：SHEET 3参照 POLYESTER(PBT), UL94 V-0, COLOR : SEE SHEET 3.

B	A	極数 CIRCUIT SIZE
18.75	22	16
17.5	20.75	15
16.25	19.5	14
15	18.25	13
13.75	17	12
12.5	15.75	11
11.25	14.5	10
10	13.25	9
8.75	12	8
7.5	10.75	7
6.25	9.5	6
5	8.25	5
3.75	7	4
2.5	5.75	3
1.25	4.5	2

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS	SCALE
mm	NTS

GENERAL TOLERANCES (UNLESS SPECIFIED)

ANGULAR TOL	±	3.0 °
4 PLACES	±	0.2
3 PLACES	±	0.2
2 PLACES	±	0.2
1 PLACE	±	0.2
0 PLACES	±	0.2

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

CURRENT REV DESC:

EC NO: 757367
DRWN: SOKUMURA01 2023/07/21
CHK'D: SAKIYAMA 2023/09/12
APPR: AIDA 2023/09/12

INITIAL REVISION:
DRWN: RWATANABE01 2017/09/15
APPR: TKANEKO 2017/09/26

molex

MICRO-LOCK PLUS 1.25 W/B
SINGLE ROW RECEPTACLE HOUSING
LOW-HALOGEN

PRODUCT CUSTOMER DRAWING


DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
2045320000-SD	PSD	000	G


THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
	A3-SIZE	204532	SEE SHEET 3	GENERAL	1 OF 3

DOCUMENT STATUS	P1	RELEASE DATE	2023/09/12 06:08:37

FORMAT number/rev/A3
Downloaded from Arrow.com.


製品形状
PRODUCT SHAPE






VIEW Z

2-13極
2-13 CIRCUIT





VIEW Y

14-16極
14-16 CIRCUIT

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS	SCALE
mm	NTS

GENERAL TOLERANCES (UNLESS SPECIFIED)		
ANGULAR TOL	±	3.0 °
4 PLACES	±	0.2
3 PLACES	±	0.2
2 PLACES	±	0.2
1 PLACE	±	0.2
0 PLACES	±	0.2

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

CURRENT REV DESC:

EC NO: 757367
DRWN: SOKUMURA01 2023/07/21
CHK'D: SAKIYAMA 2023/09/12
APPR: AIDA 2023/09/12

INITIAL REVISION:
DRWN: RWATANABE01 2017/09/15
APPR: TKANEKO 2017/09/26

molex

MICRO-LOCK PLUS 1.25 W/B
SINGLE ROW RECEPTACLE HOUSING
LOW-HALOGEN

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
2045320000-SD	PSD	000	G

THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
	A3-SIZE	204532	SEE SHEET 3	GENERAL	2 OF 3

DOCUMENT STATUS	P1	RELEASE DATE	2023/09/12 06:08:37

Downloaded from Arrow.com.

△3 適合製品及び各種仕様書 APPLICABLE PRODUCTS AND VARIOUS SPECIFICATIONS

	PART NUMBER	SPECIFICATION NUMBER
梱包仕様書 PACKAGING SPECIFICATION	204532**0*	2045329200 PS 200

	PART NUMBER	PLATING TYPE	WIRE SIZE(AWG)
適合ターミナル APPLICABLE TERMINAL	5054311000	TIN	#26-30
	5054311100	GOLD	

SMT

		TIN PLATING			GOLD PLATING	
適合嵌合相手 MATE WITH	タイプ TYPE	VERTICAL	RIGHT ANGLE	VERTICAL (FOR POTTING)	VERTICAL	RIGHT ANGLE
		2-16 CIRCUIT				
	製品番号 PART NUMBER	204530**7*	204529**7*	205957**7*	204530**** 3, 5, 8	204529**** 3, 5, 8
製品仕様書 PRODUCT SPECIFICATION		2045320000-PS PS 000		2045320001-PS PS 000	2045320000-PS PS 001	
コネクタ取扱説明書 APPLICATION SPECIFICATION		5055650000-AS PS 000				

THROUGH HOLE

		TIN PLATING	
適合嵌合相手 MATE WITH	タイプ TYPE	VERTICAL	RIGHT ANGLE
		2-16 CIRCUIT	
	製品番号 PART NUMBER	220097**7*	220098**7*
製品仕様書 PRODUCT SPECIFICATION		2045320002-PS PS 000	
コネクタ取扱説明書 APPLICATION SPECIFICATION		5055650000-AS PS 000	

WIRE TO WIRE

		TIN PLATING
適合嵌合相手 MATE WITH	タイプ TYPE	2-9 CIRCUIT
	製品番号 PART NUMBER	2145252***
製品仕様書 PRODUCT SPECIFICATION		5055650003-PS PS 000
コネクタ取扱説明書 APPLICATION SPECIFICATION		5055650000-AS PS 000

製品嵌合図は各嵌合相手図面を参照のこと
MATING VIEW : REFER TO EACH "MATE WITH" PART DRAWING.

△4 204532**0* 発注番号一覧 ORDER NUMBER LIST

BLACK	NATURAL (WHITE)	HOUSING COLOR
2045321601	2045321600	16
2045321501	2045321500	15
2045321401	2045321400	14
2045321301	2045321300	13
2045321201	2045321200	12
2045321101	2045321100	11
2045321001	2045321000	10
2045320901	2045320900	9
2045320801	2045320800	8
2045320701	2045320700	7
2045320601	2045320600	6
2045320501	2045320500	5
2045320401	2045320400	4
2045320301	2045320300	3
2045320201	2045320200	2
発注番号 ORDER NUMBER		極数 CIRCUIT SIZE

梱包形態：ポリ袋
PACKAGING : POLYBAG PACKAGE

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS	SCALE
mm	NTS

GENERAL TOLERANCES (UNLESS SPECIFIED)

ANGULAR TOL	±	3.0 °
4 PLACES	±	0.2
3 PLACES	±	0.2
2 PLACES	±	0.2
1 PLACE	±	0.2
0 PLACES	±	0.2

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

CURRENT REV DESC:

EC NO: 757367
DRWN: SOKUMURA01 2023/07/21
CHK'D: SAKIYAMA 2023/09/12
APPR: AIDA 2023/09/12

INITIAL REVISION:
DRWN: RWATANABE01 2017/09/15
APPR: TKANEKO 2017/09/26

molex

MICRO-LOCK PLUS 1.25 W/B
SINGLE ROW RECEPTACLE HOUSING
LOW-HALOGEN

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
2045320000-SD	PSD	000	G

THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
	A3-SIZE	204532	SEE CHART	GENERAL	3 OF 3

DOCUMENT STATUS	P1	RELEASE DATE	2023/09/12 06:08:37

Downloaded from Arrow.com.