

B

B

Notes:

- 1) EACH CABLE ASSEMBLY TO BE INDIVIDUALLY BAGGED.
- 2) 50μIN GOLD PLATING ON PLUG CONTACTS
- 3) CABLE CONSTRUCTION
 - 24AWG STRANDED WIRE
 - 4-PAIR, CAT6, U/UTP, TYPE CMG
 - PVC JACKET
- 4) OVERMOLDED STRAIN RELIEF PVC, COLOR TO MATCH JACKET COLOR

P/N Key:

BC-6Uxyyz

UOM

M = Meters
F = Feet

Length

Meters = xx.x (00.3 – 30.0)
Feet = xxx (001 – 100)
(500 = 0.5ft)

Color


E = Blue O = Orange
G = Grey R = Red
K = Black W = White
N = Green Y = Yellow

Example Part Numbers*


Feet		
P/N	Color	Length
BC-6UG500F	Grey	0.5 ft.
BC-6UG001F	Grey	1.0 ft.
BC-6UK010F	Black	10.0 ft.
BC-6UK025F	Black	25.0 ft.
BC-6UW501F	White	1.5 ft.

Meters		
P/N	Color	Length
BC-6UW005M	White	0.5m

* For part numbers not shown, follow part number key format.



THIRD ANGLE PROJECTION




DO NOT SCALE DRAWING

DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE

DIMENSIONS: INCHES [METRIC]

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ±.005 [0.13] ANGLES ARE ± 1°

SHEET NO. 1 OF 1



bel

206 Van Vorst Street
Jersey City, NJ 07302
+1 201 432 0463
<http://www.belfuse.com>


TITLE:

Bel Patchcord Assembly, C6 U/UTP


THIS DRAWING AND THE SUBJECT MATTER SHOWN THEREON ARE CONFIDENTIAL AND THE PROPRIETARY PROPERTY OF BEL FUSE, INC. AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT PRIOR WRITTEN CONSENT OF BEL FUSE, INC.

DRN BY:	XYQ	DATE	05/17/17
APPD BY:	HU	DATE	05/17/17
DWG NO.	CT999141	REV.	A4

DATE	REV	ECN	APP'D. BY
05/17/17	A0	Released	HU
08/07/17	A1	11059	KC
12/03/19	A2	11479	ADB
09/12/22	A3	12041	GWL
06/27/24	A4	12390	KAW



Wiring Map: 568B Standard



A

A