

KNAC0404ASM Nactus Optical System with 4 Lenses; Module dimensions: 50,00mm x 50,00mm; Lens pitch: 25.40 mm

Free Search

Search

Search Items

LEDs Manufacturers

-choose-

LEDs

-choose-

Product ranges

-choose-

Diameter (mm)

-min-

-max-

Side (mm)

-min-

-max-

Height (mm)

-min-

-max-

Material

-choose-

Viewing Angle (FWHM) ...

-min-

-max-

... or select angle from list

-choose-

Type of Optics

-choose-

Single vs Multi Optics

-choose-

Connector

-choose-

Application required

-choose-

Required Application

Search Items

Reset all search items

Accessories

Box for PCB and Electronic Components

Cover for Reflectors

Heatsinks

PCB for testing

Protective Lens for Seoul® Acriche2

Certifications & Statement

ISO 9001:2008 Certifications

RoHS Compliance

REACH Compliance

Conflict Mineral Statement


KHATOD LENS Use and

Maintenance

Reserved Area

Versione 1.9.6_ev3_u4_B

Nactus Small Optical System
KNAC0404ASM



KHATOD

Description

This multi-lens array can be used in the following application: Street Light - IESNA, Residential Light, Garden Light, Architectural Light and any application in General Lighting & Wide Area Lighting Indoor/Outdoor.

Module dimensions: 50,00mm x 50,00mm; Lens pitch: 25.40 mm; Height: 6.97mm

LED (Nominal LED Luminous Flux): 250lm

BEAM DIVERGENCE (Beam Angle Degree): 120° Symm

IES TYPE (IESNA Distribution Type): Vs Short

Material: PMMA

Full angle at 50% from maximum: ~ 130°

Full angle at 10% from maximum: ~ 152°

The light spots here represented refer to tests carried out with LEDs with 3mm dome, ~ 250lm

NACTUS SMALL. Different models offer countless opportunities to customize your lighting fixtures. Each of the modules performs a different light spot. Use NACTUS modules of the same type or mix different models in the same structure to create lighting fixtures of desired dimensions and configurations.

The arrow mark on the module surface helps a correct positioning in your application:

- Street Lighting = the arrow points to the street side

- General Lighting, Indoor/Outdoor = the arrow follows the light direction from the LED source

Lens pitch: 25.40 mm.

Insert a screw into the central hole to fasten the module to the PCB.

The modules hold the part number for easy identification; clear fine-frosted finishing.

No need to develop any photometric analysis: every model has individual photometry.

Designed for LEDs of latest generation, from 100 lm/W to 300 lm/W.

On request, the multi-lens array is available with PCB for testing (LED Board (DEMO)).

The NACTUS Optica System is Patented and EN 62471:2010 approved.

----- Part Number -----


KNAC0404ASM [optic]

KNAC0404ASM1X [optic + LED Board (DEMO)]

Product images are for illustrative purposes only.

All the data contained in this page are the propriety of Khatod Optoelectronic Srl and may change without prior notice.

Only the Part Numbers stated in Khatod order confirmations are the valid and active ones.



Download Area

[Download all files >>](#)

KNAC0404ASM technical detail

knac0404asm xbd cree eulumdat

knac0404asm xbd cree iesna

knac0404asm xml cree eulumdat

knac0404asm xml cree iesna

knac0404asm xml2 cree eulumdat

knac0404asm xml2 cree iesna

knac0404asm xpe cree eulumdat

knac0404asm xpe cree iesna

knac0404asm xpe2 cree eulumdat

knac0404asm xpe2 cree iesna

knac0404asm xpg cree eulumdat

knac0404asm xpg cree iesna

knac0404asm xpg2 cree eulumdat

knac0404asm xpg2 cree iesna

knac0404asm xte cree eulumdat

knac0404asm xte cree iesna

knac0404asm rebel es luxeon eulumdat

knac0404asm rebel es luxeon iesna

knac0404asm rebel luxeon eulumdat

knac0404asm rebel luxeon iesna

knac0404asm t luxeon eulumdat

knac0404asm t luxeon iesna

knac0404asm tx luxeon eulumdat

knac0404asm tx luxeon iesna

knac0404asm z es luxeon eulumdat

knac0404asm z es luxeon iesna

knac0404asm nsw219a nichia eulumdat

knac0404asm nsw219a nichia iesna

knac0404asm oslon square osram eulumdat

knac0404asm oslon square osram iesna

knac0404asm sz5m1 seoul eulumdat

knac0404asm sz5m1 seoul iesna

knac0404asm phenix proligh eulumdat

knac0404asm phenix proligh iesna

knac0404asm lh351z samsung eulumdat

knac0404asm lh351z samsung iesna

knac0404asm h35c1 series lg eulumdat

knac0404asm h35c1 series lg iesna

[Samples Request](#)

[Quotations Reque!](#)

[E-mail](#)

0 Tweet