



Fittings for metallic conduits with plastic coating PCS12-EI

PCS-EI End Insert, Article number: 166-31801



Images (1)

Downloads

Features

- Single part
- Caps end of conduit

Certifications & Approvals



Application


Nickel plated brass.

PCS-EI End Insert is suitable for following markets and industries



More products in this product group

[Fittings for metallic conduits with plastic coating >](#)



Base Data

Colour	Metal (ML)
Description Short (BMEcat) (max. 150 characters)	Metallic End Insert ø12mm
GLOBAL PART DESCRIPTION	PCS12-EI-NPB-ML
Metallic Fitting Type	End insert
Pack Cont.	10 pcs.
Package Quantity per	bag
Product Family	PCS-EI End Insert
Product Group	Fittings for metallic conduits with plastic coating
Type of connection	Thread
Variant	Straight

Product Dimensions

Height (H)	3.6 mm
Length (L)	16.3 mm

Min. Bore Size (B)	8.6 mm
Nominal $\varnothing$	12 mm
Nominal $\varnothing$	1/2 "
Outside $\varnothing$ max (OD max.)	16.1 mm

Material and Specifications

ELV compliant (Article 4 - 2)	YES
Halogenfree	Yes
Hazardous good	No
IP-Rating	IP65
Material	Nickel Plated Brass (NPB)
Operating Temperature - °C	-100 °C to +300 °C
Specifications	 

Logistics and Packaging

More Information

ETIM 5.0	EC001180
ETIM 6.0	EC001180

Competences



Cable Protection Conduits

No cable can meet the demands posed today in terms of abrasion resistance, tensile strength and form consistency or impact resistance without having appropriate cable protection. Cable protection tubes...

[Cable Protection Conduits >](#)

Accessories



LFHCS12
166-30900
Metallic conduits with plastic coating



PCS12
166-30701
Metallic conduits with plastic coating

Similar products



PCS10-EI
166-31800
Fittings for metallic
conduits with plastic
coating

PCS16-EI
166-31802
Fittings for metallic
conduits with plastic
coating

PCS20-EI
166-31803
Fittings for metallic
conduits with plastic
coating

PCS25-EI
166-31804
Fittings for metallic
conduits with plastic
coating

PCS32-EI
166-31805
Fittings for metallic
conduits with plastic
coating

PCS40-EI
166-31806
Fittings for metallic
conduits with plastic
coating

[Show all](#) ▾

Stay in touch with us!



Global Company

About us
Worldwide
Philosophy
Environment & Quality
Corporate Social
Responsibility
Product Development
E-Business
ACADEMY
Careers
MADE FOR REAL

Products

Product overview
Cable Ties and Fixings
Insulation
Cable Protection Systems
Electrical Installation
Identification Systems
Application Tooling
Connectivity

Competences

Cable Ties
Heat Shrink Tubing
Industrial Identification
and Self-Adhesive Labels
Cable Protection
Conduits
Electrical Installation
Electrical tape
Wire connectors
Cable rods
Downlight covers
Cable jointing
Gel-filled cable joints
Cable Tie Guns
Connectivity Products
RFID tracking
Cable tie mounts
Thermal Transfer Printer
P-Clamp
Wiring ducts
Cable clips for edges
Cable management high
temperature
applications

Markets & Industries

Automotive Industry
Solar plants
Wind turbines
Shipbuilding
Panel building
Rail industry
Food Industry
Chemical Industry
Aerospace Industry
Defence Industry

Media Centre

Videos
Product Catalogue
2018/2019
Automotive Catalogue
2016/2017
Connectivity Catalogues
2016/2017
Brochures
Software & Drivers
Helatag & Helafix
Templates
Manuals & Operating
Instructions

Events

Update: 16/09/2018

You can easily accept or reject the cookies on this site by choosing one of the following links:

[I accept cookies](#)

[I refuse cookies](#)

[Privacy](#)

[Contact](#) [Terms of Service](#) [Imprint](#) [Privacy Policy](#)

[statement](#)