DWG NO.	SH	CUSTOMER	CUSTOMER P/N	CUST. REV
1-0156	1			

DATA CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO EMERSON CONNECTIVITY SOLUTIONS AND SHALL NOT BE DISCLOSED, COPIED OR USED FOR PROCUMENT OR MANUFACTURE WITHOUT EXPRESS WRITTEN PERMISSION

REVISIONS

REV	DESCRIPTIONS	DATE	APPROVED
AF	ECO 53317	6/20/11	TKO

DASH NO	CABLES ACCOMODATED	ØA	B FLATS	C FLATS	ASEMBLE PER
-7	TRC-50-2/TRC-75-2	.750	.687	.625	TAI-175
-8	8227, BELDEN				TAI-116
-9	TWC-78-2, RG-108 TWC-124-2				
-10	754E, W.E.CO., RG-22				
-11	760A, W.E.CO.				
-12	16PEVL, W.E.CO.				TAI-131
-13	TRF-59, TIMES				TAI-175
-13A	8232, BELDEN				
-14	21-529, ESSEX 8233, BELDEN				
-14A	TRC-50-4A	.990	.875	.875	
-15	21-583, ESSEX				
-16	21-950, ESSEX				TAI-116
-26	275-3962, MICROOOT	.750	.687	.625	TAI-175
-29	TWC-124-1A				TAI-116
-32	TRC-50-1				TAI-175
-33	TRC-75-1				TAI-124
-42	21-204, ESSEX				TAI-175
-46	9860, BELDEN				TAI-116
-47	MI7/176-00002				
-54	89207, BELDEN				
-55	89272 BELDEN				
-61	5012W5812, RAYCHEM	.990	.875	.875	TAI-175
-62	7518A0811, RAYCHEM				



-9 SHOWN

4. CONCENTRIC TWINAX/TRIAX "C" STYLE CABLE PLUG W/SOCKET CENTER CONTACT

3 DIM IS MAX WHEN ASSEMBLED TO CABLE

2. INTERFACE: TCS-PL80

1 FINISH: TFS-1A (NICKEL)

NOTES: UNLESS OTHERWISE SPECIFIED.

INTERPRET DRAWING PER MIL-STD-100. DIMENSIONS ARE IN INCHES AND INCLUDE FINISH THICKNESS UNLESS OTHERWISE SPECIFIED.

TOL: UNLESS SPECIFIED .XX ± .01 .XXX ± .005 .XXXX ± .0010 ANGLE ± 1° 00' CRITICAL

cinch CONNECTIVITY SOLUTIONS
Cinch Connectivity Solutions
299 Johnson Ave. Ste. 100
Waseca, MN 56093
1-800-247-8256

DRN	BPK	6/20/11
CHK	TKO	6/22/11
QUALITY		
MANUF		
APPROVED		
PROE FILE NO.	1-0156	

MATERIAL:

FINISH: 1

DO NOT SCALE DWG

TITLE: PL80

SIZE	CAGE CODE	DRAWING NO.	REV.
B	14949	1-0156	AF

SCALE	DATE	SHEET
1/1	4/28/89	1 OF 2

N/A	
BLANK LENGTH (REF. ONLY)	
N/A	
SURFACE AREA	

Downloaded from Arrow.com.

Please read our datasheet & drawing disclaimer here.