

[Search Only Products /](#)

LaserTab Metallized Polyester Labels



LaserTab Metallized Polyester Labels

Part Number:

LAT-20-773-2.5

Material:

Metallized Polyester

Dimensions:

0.75 in H x 1.5 in W

UOM:

Pack of 42 Sheets

Color:

Silver

ADD TO CART

1

PEOPLE ALSO VIEWED

OVERVIEW

Metallized Polyester (B-773) is designed for applications like rating plates that use alphanumerics, barcodes, graphics and logos and require nameplate-like quality.



- Silver polyester film with a permanent acrylic pressure sensitive adhesive and a matte topcoat specifically formulated for laser printing
- Excellent chemical, oil and water resistance and meets the requirements of a halogen-free material per DIN VDE 0472 part 815
- UL Recognized component and CSA Accepted material when printed with designated laser printer toners
- Operating temperature of -85 to 248° F (-65 to 120° C)

SPECIFICATIONS

Anti-Skid Surface?	N/A
Material Number	B-773
Dimensions	0.75 in H x 1.5 in W
UOM	Pack of 42 Sheets
Finish	Matte
Indoor or Outdoor Use	N/A
Maximum Service Temperature °F	248 °F
Minimum Service Temperature °F	-85 °F
Printable Area Dimensions	0.75 in H x 1.5 in W
Printable Area Height	0.75 in
Printable Area Width	1.5 in
Product Number	29750
UPC	662820297505
Quantity per Card or Sheet	60
Sheet Height	11 in
Sheet Width	8.5 in
Tamper Indication Type	N/A
Thickness	0.0048 in
Trade Name	LaserTab®
Adhesive Type	Acrylic
Applications	Rating Plates
Color	Silver

Header	No Header
Material	Metallized Polyester
Material Properties	Laser Toner-receptive, Metallized
Resistance Properties	Chemical-Resistant, High Temperature-Resistant, Humidity-Resistant, UV-Resistant, Weather-Resistant
Shape	Rectangle

SUPPORT

LITERATURE

LAT-20 LaserTab Set Up Sheet

Solutions

- Floor Marking Guide
- GHS Label Compliance
- Lockout Tagout Compliance
- Arc Flash Labeling Requirements
- Cable and Wire Label Options
- Product and Barcode Labeling
- Brand Protection Solutions

Services

- Lockout Tagout Services
- Arc Flash Services
- Confined Space Services
- Visual Workplace Services
- Hazcom GHS Services
- Software Programming & Integration
- Label Template & File Conversion
- Printer Use & Training
- Printer Preventative Maintenance
- Toll and Custom Coating
- Authentication & Tracking Services

Help

- Contact Us
- Knowledge Center
- Printer Drivers & Firmware
- Brady Software Updates
- Safety Data Sheets
- Technical Data Sheets
- WEEE-RoHS Compliance
- Product Certification
- Printer Registration

Resources

- Find a Distributor
- Printer Selection Tool
- Label Selection Tool
- Digital Catalog
- Request a Catalog



Brady
(NYSE:BRC)
is a
manufacturer
of complete
solutions
that
identify and
protect
people,
products
and places.
Brady's
products
help
customers
increase
safety,
security,
productivity
and
performance
and include
high-
performance
labels,
signs, safety
devices,
printing
systems
and
software.

Contact
6555
W.
Good
Hope
Rd.
Milwaukee
WI
53223
Phone:
888-
250-
3082
Hours:
7am-
6pm
CST
Monday
-
Thursday;
Friday
7am-
5pm
CST

About
Corporation
Privacy
Policy
Terms
and
Conditions
Terms
of Use
ISO
Certificates

Other
Brady
Sites
Distributor
Portal
International
Sites
Safety
Services
&
Software
Smart
ID
Brand
Protection



© 2018 Brady Worldwide, Inc.