



Part Number : [989821016](#)

Product Description : 2.54mm Pitch MOX Receptacle Kit, Dual Row, 20 Circuits, Blue

Series Number : 98982

Status : Active

Product Category : Connector Housings

Engineering Part Number : 74106316



Documents and Resources

Drawings

[989821016_sd.pdf](#)

[PK-98982-002-001.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)


[Creo](#)

Specifications

[AS-98982-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	98982
Description	2.54mm Pitch MOX Receptacle Kit, Dual Row, 20 Circuits, Blue
Application	Power, Wire-to-Board
Product Name	MOX
UPC	822348817214

Physical

Circuits Detail	20
Circuits (maximum)	20
Color - Resin	Blue
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	1.660/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm

Pitch - Termination Interface	2.54mm
Polarized to Mating Part	No
Ports	1
Stackable	No
Temperature Range - Operating	-40° to +125°C

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	Please Contact Molex for Details

Use with Part(s)

Description	Part Number
MOX Female Crimp Terminals	<u>98658</u>

Application Tooling

Global

Description	Part Number
Extractor Tool for MOX 0.635mm Receptacle Crimp Terminals	<u>638138400</u>
Extractor Tool for MOX 0.635mm Receptacle Crimp Terminals	<u>638244400</u>

This document was generated on Jan 05, 2026