




2-1969594-4 Product Details

 Share

 Print

 Email



 Active

Economy Power Connectors

HSG,REC,PANEL MOUNT,DUALROW,EP2.5

2-1969594-4 

TE Internal Number: 2-1969594-4

Product Highlights [View All](#)

- Economy Power 2.5 Product Line
- Connector
- Wire-to-Wire
- Applies To Wire/Cable
- 24 Positions

Pricing & Availability

Request Sample

Add to My Part List

Buy Product through Distributor

Feedback

DocumentsFeaturesCompliance

Please Note:

Use the Product Drawing for all design activity

Product Type Features

Product Line	Economy Power 2.5
Product Type 	Connector
Connector Type	Housing
Sealed	No

Mechanical Attachment

Mating Retention Type	Latch(ing)
-----------------------	------------

Electrical Characteristics

Contact - Rated Current (A)	7.5 
Operating Voltage Reference	AC
Operating Voltage (VAC)	250

Termination Features

Wire/Cable Size (AWG)	22 – 26
Wire/Cable Size (mm²)	0.13 – 0.33
Termination Method to Wire/Cable	Crimp

Dimensions

Length (X-Axis) (mm [in])	32.89 [1.295]
Width (Z-Axis) (mm [in])	10.32 [0.406]
Profile Height (Y-Axis) (mm [in])	19.97 [0.786]

Body Features

Mating Retention	With
------------------	------

Contact Features

Contact Type	Pin
--------------	-----

Housing Features

Centerline (mm [in]) 	2.50 [0.098]
Connector Style	Receptacle
Housing Color	White
Housing Material	Nylon - GF

Configuration Features

Number of Positions 	24
Number of Rows	2

Industry Standards

RoHS/ELV Compliance 	RoHS compliant, ELV compliant
Lead Free Solder Processes 	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant
UL Flammability Rating	UL 94V-0 

Environmental

Operating Temperature (°C [°F])	-25 – +105 [-13 – +221]
---------------------------------	-------------------------

Conditions for Usage

Applies To	Wire/Cable
Glow Wire Rating	Glow Wire
Accepts Wire Insulation Diameter, Range (mm [in])	1.30 – 1.70 [0.051 – 0.067]

Operation/Application

Application Use	Wire-to-Wire
Contact Transmits (Typical Application)	Power

Packaging Features

Packaging Method	Bag/Box
------------------	---------

Other

Brand	TE Connectivity
Comment	Free Hanging

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

About TE
Investors
News Room
Supplier Portal
Careers
Terms & Conditions
Privacy Policy
Global Accessibility Statement

Quick Links

Distributor Inventory
Product Cross Reference
Documents & Drawings
Product Compliance Support Center
Site Map

Customer Support

Email or Chat With Us
Find a Phone Number
Knowledge Base
Manage Your Account

Keep Me Informed

