

SEARCH



Printers and Scanners / Desktop Printers, Labels and Accessories / Bradyprinter PR Plus Printer, Labels and Accessories / Bradyprinter PR Plus Printer Labels /

Paper Labels



Paper Labels

Part Number:

THT-55-402-3

Label/Tape Size:

2 in H x 4.125 in W

Material:

Paper

For Use with Printer:

BBP®81 Label Printer, BRADY IP® Series
Label Printer, BradyPrinter i7100,
BRADYPRINTER PR Plus Series Label Printer

Material Number:

B-402

Color:

White

Quantity per Roll:

3000

ADD TO CART

1

PEOPLE ALSO VIEWED

OVERVIEW

Brady® B-402 Paper material for thermal transfer print technology is an economical solution for general purpose labeling needs.

- Paper labels feature a permanent acrylic adhesive
- Ideal for labeling applications requiring a low cost label material
- RoHS compliant to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC
- Service temperature of -70 to 140° F (-56 to 60° C)

SPECIFICATIONS

Anti-Skid Surface?	N/A
Material Number	B-402
Dimensions	2 in H x 4.125 in W
UOM	Roll of 3000 Labels
Finish	Matte
Indoor or Outdoor Use	N/A
Label/Tape Size	2 in H x 4.125 in W
Maximum Service Temperature °F	140 °F
Minimum Service Temperature °F	-94 °F
Printable Area Dimensions	2 in H x 4 in W

Printable Area Height	2 in
Printable Area Width	4 in
Product Number	14953
UPC	662820149538
Quantity per Roll	3000
Quantity per Row	1
Secondary Label Included	Secondary Label is Not Included
Tamper Indication Type	Tamper-Resistant
Thickness	0.0035 in
Adhesive Type	Acrylic
Applications	General & Industrial ID
Color	White
For Use with Printer	BBP®81 Label Printer, BRADY IP® Series Label Printer, BradyPrinter i7100, BRADYPRINTER PR Plus Series Label Printer
Label/Media Format	Roll
Material	Paper
Material Properties	N/A
Print Technology	Thermal Transfer
Resistance Properties	Abrasion-Resistant, Humidity-Resistant, UV-Resistant
Shape	Rectangle
Suggested Ribbon Series	R6100

Solutions

[Floor Marking Guide](#)
[GHS Label Compliance](#)
[Lockout Tagout Compliance](#)
[Arc Flash Labeling Requirements](#)
[Cable and Wire Label Options](#)
[Product and Barcode Labeling](#)
[Brand Protection Solutions](#)

Services


[Lockout Tagout Services](#)
[Arc Flash Services](#)
[Confined Space Services](#)
[Visual Workplace Services](#)
[Hazcom GHS Services](#)
[Software Programming & Integration](#)
[Label Template & File Conversion](#)
[Printer Use & Training](#)
[Printer Preventative Maintenance](#)
[Toll and Custom Coating](#)
[Authentication & Tracking Services](#)

Help

[Contact Us](#)
[Knowledge Center](#)
[Printer Drivers & Firmware](#)
[Brady Software Updates](#)
[Safety Data Sheets](#)
[Technical Data Sheets](#)
[WEEE-RoHS Compliance](#)
[Product Certification](#)
[Printer Registration](#)

Resources

[Find a Distributor](#)
[Printer Selection Tool](#)
[Label Selection Tool](#)
[Digital Catalog](#)
[Request a Catalog](#)



Brady
(NYSE:BRC)
is a
manufacturer
of complete
solutions
that
identify and
protect
people,
products
and places.
Brady's
products
help
customers
increase
safety,
security,
productivity
and
performance
and include
high-
performance
labels,
signs, safety
devices,
printing
systems
and
software.

Contact
6555
W.
Good
Hope
Rd.
Milwaukee
WI
53223
Phone:
888-
250-
3082
Hours:
7am-
6pm
CST
Monday
-
Thursday;
Friday
7am-
5pm
CST

About
Corporation
Privacy
Policy
Terms
and
Conditions
Terms
of Use
ISO
Certificates

Other
Brady
Sites
Distributor
Portal
International
Sites
Safety
Services
&
Software
Smart
ID
Brand
Protection



2018 Brady Worldwide, Inc.