HellermannTyton

Specification Sheet

Part Number: 132-00011



Unique two piece tie allows parallel entry and exit through the head for easy assembly.

High impact, heat stabilized material gives strength needed for trucking and heavy equipment applications.

Article Number	132-00011
Type	BT105L
Color	Black (BK)
Quantity Per	pack
Product Description	The button head tie is a two piece tie providing for parallel entry and exit through the head. The strap contains serrations on both sides, and has two opposed pawls recessed within a domed head. This design allows the strap to be directed clockwise or counter-clockwise prior to insertion into the head, enabling bi-directional looping.
Short Description	Button Head Cable Tie, 15.0" Long, 4.3" Max Bundle Dia, 105lb, PA66HIRHSUV/PA66HS, Black, 50/pkg
Global Part Name	BT105L-PA66HIRHSUV/PA66HS-BK

Downloaded from Arrow.com.

Minimum Tensile Strength (Imperial)	105
Minimum Tensile Strength (Metric)	467
Length L (Imperial)	15.0
Length L (Metric)	381.5
Fixation Method	Button Head
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Outside Serrated
Width W (Imperial)	0.22
Width W (Metric)	5.6
Bundle Diameter Min (Imperial)	0.25
Bundle Diameter Min (Metric)	6.4
Bundle Diameter Max (Imperial)	4.33
Bundle Diameter Max (Metric)	110.0
Mounting Hole Diameter D (Metric)	22.0 mm

Downloaded from Arrow.com.

Material	Polyamide 6.6 heat stabilized (PA66HS) Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV PA66HS
Material Cable Tie	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Head	Polyamide 6.6 heat stabilized (PA66HS)
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature intermittant, 1000 hours	+320°F (+160°C)
Operating Temperature intermittant, 5000 hours	+257°F (+125°C)
Operating Temperature intermittant, 500 hours	+329°F (+165°C)
Reach Compliant (Article 33)	Yes

Package Quantity (Imperial)	50
Package Quantity (Metric)	50
Customs Number	3926909988

Downloaded from Arrow.com.

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

Downloaded from Arrow.com.