

[Products](#) / [CEC Series](#)


## CEC Series

### CONDUCTIVE CAPS FOR THREADED CONNECTORS

CEC Series conductive caps are for all common sizes of threaded electrical and electronic connectors. In addition to dissipating electrostatic charges, they provide an electrical shield over the end of the connector.

- Meet spec MS/AS 90376
- Also suitable for protecting non-threaded bayonet type connectors

*This product has been fabricated from a conductive material that:*

- Surface resistivity of less than  $1 \times 10^5$  ohms/square in accordance with ASTM test method D-257-78*

**Material:** Conductive polyethylene copolymer (EVA)  
**Standard Color:** Black




[See Purchasing Options](#)

*For additional material and color options, contact customer service at 888.CAPLUGS.*

*Note: Micropack sizes have a minimum 3 day lead time.*

[See Related Products](#)

## Purchasing Options



### Filter using your product's dimensions

Enter minimum and maximum measurements to filter the list.

**Dim A (In)**   **Dim B (In)**   **Dim C (In)**   **Dim D (In)**

MIN (IN)      MAX (IN)


25 Part Sizes

Show

10

Item #	To Cap Nominal Thread Size	Dim A (In)	Dim B (In)	Dim C (In)	Dim D (In)		
CEC-04	1/4	0.244	0.48	0.49	0.304	<input type="button" value="FREE SAMPLE"/>	<input type="button" value="+ SELECT ITEM"/>
CEC-05	5/16	0.304	0.56	0.56	0.364	<input type="button" value="FREE SAMPLE"/>	<input type="button" value="+ SELECT ITEM"/>
CEC-06	3/8	0.368	0.62	0.51	0.428	<input type="button" value="FREE SAMPLE"/>	<input type="button" value="+ SELECT ITEM"/>
CEC-07	7/16	0.430	0.71	0.63	0.510	<input type="button" value="FREE SAMPLE"/>	<input type="button" value="+ SELECT ITEM"/>
CEC-08	1/2	0.487	0.73	0.50	0.547	<input type="button" value="FREE SAMPLE"/>	<input type="button" value="+ SELECT ITEM"/>
CEC-10	5/8	0.607	0.84	0.50	0.667	<input type="button" value="FREE SAMPLE"/>	<input type="button" value="+ SELECT ITEM"/>
CEC-12	3/4	0.730	0.97	0.50	0.790	<input type="button" value="FREE SAMPLE"/>	<input type="button" value="+ SELECT ITEM"/>
CEC-14	7/8	0.852	1.15	0.50	0.912	<input type="button" value="FREE SAMPLE"/>	<input type="button" value="+ SELECT ITEM"/>
CEC-16	1	0.992	1.23	0.50	1.052	<input type="button" value="FREE SAMPLE"/>	<input type="button" value="+ SELECT ITEM"/>
CEC-18	1-1/8	1.101	1.36	0.56	1.161	<input type="button" value="FREE SAMPLE"/>	<input type="button" value="+ SELECT ITEM"/>

< PREVIOUS   **1**   2   3   NEXT >

Please take advantage of our **free samples** to test parts in your specific application/environment before ordering.

## Related Products

<p><b>SEC</b> Static Dissipative Caps for Threaded Connectors</p> <p><input type="button" value="View Details"/></p>	<p><b>C</b> Utility Caps</p> <p><input type="button" value="View Details"/></p>	<p><b>MSC</b> ESD Connector Caps and Plugs</p> <p><input type="button" value="View Details"/></p>	<p><b>ECP</b> Ergonomic Center Pull-Tab Plug</p> <p><input type="button" value="View Details"/></p>	<p><b>AS138</b> AS138 Electrical Connector Dust Caps</p> <p><input type="button" value="View Details"/></p>
--	---	---	---	---

Need something custom or want to discuss your options?

### PRODUCTS

Caps  
 Plastic Plugs  
 Masking  
 Tubing, Netting, & Containers  
 Hose Guard / Spiral Wrap  
 More Product Protection

### RELATED PRODUCTS

Evergreen Labware

Tri-Star Thread Protectors

### MATERIALS

Polyethylene

### INDUSTRIES

Medical  
 Automotive  
 Electronics  
 Aviation  
 Hydraulics  
 Evergreen Labware

### APPLICATIONS

Masking  
 Pipe & Flange Protection  
 Compressed Gas  
 Packaging & Netting  
 Hose Protection & Bundling

### CUSTOM PARTS

Custom Parts  
 Request a Quote

### SERVICE & SUPPORT

Find a Sales Representative  
 Video Library  
 Color Chart  
 Download Literature  
 Request a Quote  
 Contact Us  
 Quality & Company Documents  
 Patents  
 Material by Temperature  
 Military & NAS Specifications  
 Shopping Cart  
 Returns  
 Cross Reference

### ABOUT CAPLUGS

About Us  
 Awards  
 Join Our Team  
 Press Room

This website uses cookies to ensure you get the best experience on our website.

[Learn more](#)