

VS-09-SD - D-SUB protective cover

1887086

<https://www.phoenixcontact.com/us/products/1887086>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

D-SUB protective cover, material: PA, housing size: 1, color: gray



Your advantages

- Usable in combination with D-SUB panel-mount frame and sleeve housing

Commercial data

Item number	1887086
Packing unit	5 pc
Minimum order quantity	1 pc
Sales key	AB19
Product key	ABNCBZ
Catalog page	Page 219 (C-2-2013)
GTIN	4017918817480
Weight per piece (including packing)	7.2 g
Weight per piece (excluding packing)	6.33 g
Customs tariff number	85389099
Country of origin	DE

VS-09-SD - D-SUB protective cover



1887086

<https://www.phoenixcontact.com/us/products/1887086>

Technical data

Product properties

Product type	Protective cover
Type	D-SUB 9

Dimensions

Width	16.5 mm
Height	23.8 mm
Length	87.6 mm

Material specifications

Color	gray
Material	Plastic
Flammability rating according to UL 94	V0
Housing material	PA

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 1000
-----------------------------	--------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP54 (in combination with the sleeve housing)
	IP65 (in combination with the panel mounting frame)
Ambient temperature (operation)	-40 °C ... 80 °C

VS-09-SD - D-SUB protective cover



1887086

<https://www.phoenixcontact.com/us/products/1887086>

Classifications

ECLASS

ECLASS-13.0	27440208
-------------	----------

ETIM

ETIM 9.0	EC002314
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

VS-09-SD - D-SUB protective cover



1887086

<https://www.phoenixcontact.com/us/products/1887086>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com