



REV	
NC	DTMH04-3P*


REVISIONS			
SYM	DESCRIPTION	DATE	APPROVED
NC	NEW RELEASE PER E.O. P19881	9-15-08	SB












TPA △3 △8



△8 SEE SHEET 2 FOR OTHER KEY ARRANGEMENTS.

7. RECEPTACLE IS RATED AT 150°C.

6. MATERIAL - HOUSING: PLASTIC; GROMMET: RUBBER.

5. THIS RECEPTACLE MATES WITH DTMH06-3S-**** AND DTM06-3S-**** PLUG. (**** = ALL MODIFICATIONS)

△4 FOR CONTACT AND WIRE PERFORMANCE AND APPLICATION CHARACTERISTICS SEE ENVELOPE DRAWING 0425-015-0000.

△3 TERMINAL POSITION ASSURANCE (TPA) LOCK PRE-MOUNTED: WMH-4P* (* = A,B,C,D KEYS).

2. DIMENSION TOLERANCE: ±.025 [.64].

1. DIMENSIONS ARE IN INCHES [mm].

NOTES: UNLESS OTHERWISE SPECIFIED

CONTACT SIZE	MIN. INSUL. O.D.	MAX. INSUL. O.D.	WIRE RANGE △4 [mm^2] REF ONLY
20	.053 [1.35]	.120 [3.05]	16-20 AWG [1.0-0.5]

	SIGNATURE & DATE
DR	J. APOSTOL 28DEC2007
CHK	9/10/08
PE	8/11/08
APPD	9/2/08
SCALE	NONE WT

RECEPTACLE
3 PIN CONT. #20
COLOR: BLACK
DTMH SERIES

ENVELOPE

EP 180 | MATL. CODE

DEUTSCH INDUSTRIAL
3850 INDUSTRIAL AVE.
HEMET, CA 92545


B | DTMH04-3P*

DWG SIZE | CODE 11139 | SHEET 1 OF 2

Downloaded from Arrow.com.

REV	
NC	DTMH04-3P*

REVISIONS			
SYM	DESCRIPTION	DATE	APPROVED
	SEE SHEET 1	9-15-08	SLB





DTMH04-3PA
-A- KEY
TPA COLOR: GREY

DTMH04-3PB
-B- KEY
TPA COLOR: BLACK

DTMH04-3PC
-C- KEY
TPA COLOR: GREEN

DTMH04-3PD
-D- KEY
TPA COLOR: BROWN

NOTES:

	SIGNATURE & DATE
DR	J. APOSTOL 28DEC2007
CHK	9/10/08
PE	D. Whitacre 8/1/08
APPD	9/2/08
SCALE	NONE

RECEPTACLE
3 PIN CONT. #20
COLOR: BLACK
DTMH SERIES

ENVELOPE

EP 180	MATL. CODE

3850 INDUSTRIAL AVE.
HEMET, CA 92545
DEUTSCH INDUSTRIAL

DWG SIZE		
B	DTMH04-3P*	
	CODE 11139	SHEET 2 OF 2

Downloaded from Arrow.com.