

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0541323362

Status:

Active

Overview:

Easy-On FFC FPC Connectors

Description:

Easy-On FFC/FPC Connector, 0.50mm Pitch, Slider Series, Right-Angle, Bottom Contact, 2.00mm Height, 33 Circuits, Gold Plating

- Documents:
- 3D Model (PDF)

Datasheet (PDF)
- Drawing (PDF)

Product Guide (PDF)
- 3D Model

RoHS Certificate of Compliance (PDF)
- Product Specification PS-54132-061-001 (PDF)

Reference Guide (PDF)
- Packaging Specification SPK-54132-001-001 (PDF)

Agency Certification

UL

E29179

General

Product Family

FFC/FPC Connectors

Series

54132

Overview

Easy-On FFC FPC Connectors

Product Name

Easy-On

Series Name

Slider

UPC

822350128421

Physical

Actuator Type

Slider

Circuits (Loaded)

33

Color - Resin

Black, Natural

Contact Position

Bottom

Durability (mating cycles max)

20

Flammability

94V-0

Mated Height

2.00mm

Material - Metal

Phosphor Bronze

Material - Plating Mating

Gold

Material - Plating Termination

Gold

Material - Resin

High Temperature Thermoplastic

Net Weight

383.047/mg

Number of Rows

1

Orientation

Right Angle

PCB Locator

No

PCB Mounting

Surface Mount

PCB Retention

Yes

Packaging Type

Embossed Tape on Reel

Pitch - Mating Interface

0.50mm

Plating min - Mating

0.102µm

Plating min - Termination

0.051µm

Polarized to PCB

Yes

Stackable

No

Surface Mount Compatible (SMC)

N/A

Temperature Range - Operating

-40° to +85°C

Wire/Cable Type

FFC/FPC

Electrical


Current - Maximum per Contact

0.5A

Voltage - Maximum

50V

Material Info



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

54132 Series

Mates With

Premo-Flex FFC Cable [15020](#)

Reference - Drawing Numbers

Packaging Specification	SPK-54132-001-001
Product Specification	PS-54132-061-001
Sales Drawing	SD-54132-064-001, SD-54132-065

This document was generated on 07/17/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION