

Type: 090823090


External dimensions: 80 x 230 x 85 mm

Weight: 600 g

| DIN rail length in mm | max. fitting length in mm | Mounting plate (thickness in mm) | External mounting brackets | External hinge* set | EMC version | Self-adhesive rubber feet set | Silicone lid seal | Sealable lid screw in steel |  |
|-----------------------|---------------------------|----------------------------------|----------------------------|---------------------|-------------|-------------------------------|-------------------|-----------------------------|--|
| TS 15                 |                           |                                  |                            |                     |             |                               |                   |                             |  |
| 218                   | 204                       | 1.5                              | •                          | •                   | •           | •                             | •                 | •                           |  |


Lid

\* = Conical form tapering downwards  
Free dimensions-tolerance to DIN 16901 - 130



Base

Maximum number of cable glands to DIN 50262\*



| M  | Corner dim. | Side |     | PG   | Corner dim. | Side |     |
|----|-------------|------|-----|------|-------------|------|-----|
|    |             | A/B  | C/D |      |             | A/B  | C/D |
| 12 | 17.25       | 40   | 6   | 7    | 17.25       | 40   | 6   |
| 16 | 25.30       | 18   | 3   | 9    | 21.85       | 27   | 3   |
| 20 | 27.60       | 14   | 2   | 11   | 25.30       | 17   | 2   |
| 25 | 37.95       | 7    | 1   | 13.5 | 27.60       | 14   | 2   |
| 32 | 48.30       | 4    | 1   | 16   | 31.05       | 12   | 2   |
| 40 | 60.95       | 3    |     | 21   | 37.95       | 7    | 1   |
| 50 | 69.00       |      |     | 29   | 48.30       | 4    |     |
| 63 | 74.75       |      |     | 36   | 60.95       | 3    |     |
|    |             |      |     | 42   | 69.00       |      |     |
|    |             |      |     | 48   | 74.75       |      |     |

|             |                |                                                                                         |                                                                                       |
|-------------|----------------|-----------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| DATE        | 17 MAY 2017    | 7330 Executive Way<br>Frederick, MD 21704<br>(301) 696-9411 voice<br>(301) 696-9494 fax |  |
| SHEET       | 1              |                                                                                         |                                                                                       |
| DESCRIPTION |                | ENCLOSURE, STANDARD, ABS<br>80 X 230 X 85MM, RAL 7035                                   |                                                                                       |
| SIZE        | DRAWING NUMBER |                                                                                         | REV                                                                                   |
| A           | 090823090      |                                                                                         | -                                                                                     |