Part Number : 500798020
Product Description : 1.25mm Pitch, PicoBlade Female Crimp Terminal, Gold (Au) Flash Plating, 28-26 AWG, Reel
Series Number : 50079
Status : Active
Product Category : Crimp Terminals



Documents and Resources

Drawings

500798020_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

510210000-AS-000.pdf

SPK-50079-001-001.pdf

510210000-PS-000.pdf

510210001-PS-000.pdf

510210006-PS-000.pdf

510211000-PS-000.pdf

510211001-PS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-

Downloaded from Arrow.com.

	DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	50079
Description	1.25mm Pitch, PicoBlade Female Crimp Terminal, Gold (Au) Flash Plating, 28-26 AWG, Reel
Application	Wire-to-Board, Wire-to-Wire
Product Name	PicoBlade
UPC	193264576357

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	125V AC (RMS)/DC

Physical

Durability (mating cycles max)	30
Gender	Female

Downloaded from Arrow.com.

Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Net Weight	10.100/mg
Packaging Type	Reel
Plating min - Mating	0.051µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.04mm max
Wire Size (AWG)	26, 28
Wire Size mm^2	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
PicoBlade Single Row Receptacle Housings	51021

Application Tooling

Global

Description	Part Number
FA2 Mechanical Feed Crimp Applicator for 1.25mm Pitch PicoBlade Female Terminals, 28-26 AWG	2130696200
Hand Crimp Tool for 1.25mm Pitch PicoBlade Crimp Terminals, 28-26 AWG	2002189700

Japan

Description	Part Number
S-1 Applicator for PicoBlade Receptacle Terminals, 32-26 AWG	570673700

Downloaded from Arrow.com.