




7-2064915-6 Product Details

[Share](#) [Print](#) [Email](#)

7-2064915-6

TE Internal Number: 7-2064915-6

 [Active](#)

Fiber Optic Cable Assemblies

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Cable Assembly
- LC ODVA Fiber Optic Cable Connector Type
- Fiber Type = 50/125 Micron
- Cable Assembly Type = LC Duplex to LC Duplex
- Multimode

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [CABLE ASSEMBLY, FIBER OPTIC, 50/125, OM3, 2 FIBER B...](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Cable Assembly
- Fiber Optic Cable Connector Type = LC ODVA
- Cable Assembly Type = LC Duplex to LC Duplex
- Cable Type = OFNR

Termination Features:

- [Fiber Type \(Micron\)](#) = 50/125
- [Mode](#) = Multimode

Body Features:

- Cable Diameter (mm [in]) = 7.5 [.295]
- Number of Fibers = 2
- Cable Color = Black
- Length (M [ft]) = 76.00 [249.34]
- Connector Color = Beige
- Protective Cap = With

Contact Features:

- Boot Body Style - Left = Standard
- Boot Color - Left = Black
- Boot Body Style - Right = Standard
- Boot Color - Right = Black
- Fibre Channel = No

Housing Features:

- Flammability Rating Type = UL OFNR

Configuration Features:

- [Cable Buffering](#) = Tight Buffered
- Connector(s) Exit Angle to Connector(s) Exit Angle = 180° to 180°

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- Brand = Tyco Electronics

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

