



[Labels](#) / [Wire and Cable Labels](#) / [Wire and Cable Label Cards](#) /

Pre-printed 5 Wire Markers



Pre-printed 5 Wire Markers

Part Number:

TMM-5-PK

Dimensions:

0.5 in H

Material:

Vinyl

Color:

Black on White

Text Legend:

5

PEOPLE ALSO VIEWED



OVERVIEW

B-702 Low-Profile Glossy Vinyl-Coated Polyester miniature wire markers from Brady® have high adhesion properties, making them ideal for wire marking and machine tool labeling.

- Card-mounted wire markers allow for quick, on-the-spot wire marking
- Glossy white vinyl topcoat with a high tack rubber-based adhesive features excellent flexibility for wrapping on thin gauge wire
- High adhesion and low profile when wrapped on wires
- Withstands mild chemicals, oil and water

SPECIFICATIONS

Material Number	B-702
Cards or Sheets per Pack	25
Dimensions	0.5 in H
UOM	Pack of 25 Cards
Finish	Gloss
Maximum Service Temperature °F	212 °F
Minimum Service Temperature °F	-40 °F
Product Number	111456
UPC	662820904885
Quantity per Card or Sheet	150

Thickness	0.0022 in
Adhesive Type	Rubber
Applications	Cable & Wire Marking, Machine Tool Labeling
Color	Black on White
Label/Media Format	Die-Cut on Cards
Material	Vinyl
Material Properties	Low Profile
Resistance Properties	Chemical-Resistant, Corrosion-Resistant, Humidity-Resistant, Oil-Resistant, UV-Resistant, Weather-Resistant
Serialization	No Serialization
Text Legend	5

Solutions

[Floor Marking Guide](#)
[GHS Label Compliance](#)
[Lockout Tagout Compliance](#)
[Arc Flash Labeling Requirements](#)
[Cable and Wire Label Options](#)
[Product and Barcode Labeling](#)
[Brand Protection Solutions](#)

Services


[Lockout Tagout Services](#)
[Arc Flash Services](#)
[Confined Space Services](#)
[Visual Workplace Services](#)
[Hazcom GHS Services](#)
[Software Programming & Integration](#)
[Label Template & File Conversion](#)
[Printer Use & Training](#)
[Printer Preventative Maintenance](#)
[Toll and Custom Coating](#)
[Authentication & Tracking Services](#)

Help

[Contact Us](#)
[Knowledge Center](#)
[Printer Drivers & Firmware](#)
[Brady Software Updates](#)
[Safety Data Sheets](#)
[Technical Data Sheets](#)
[WEEE-RoHS Compliance](#)
[Product Certification](#)
[Printer Registration](#)

Resources

[Find a Distributor](#)
[Printer Selection Tool](#)
[Label Selection Tool](#)
[Digital Catalog](#)
[Request a Catalog](#)
[Interactive Facility Map](#)



Brady
(NYSE:BRC)
 is a
 manufacturer
 of complete
 solutions
 that
 identify and
 protect
 people,
 products
 and places.
 Brady's
 products
 help
 customers
 increase
 safety,
 security,

Contact
6555
W.
Good
Hope
Rd.
Milwaukee
WI
53223
Phone:
888-
250-
3082
Hours:
7am-
6pm
CST
Monday
-

About
Corporation
Privacy
Policy
Terms
and
Conditions
Terms
of Use
ISO
Certificates

Other
Brady
Sites
Distributor
Portal
International
Sites
Safety
Services
&
Software
Smart
ID
Brand
Protection



2018 Brady Worldwide, Inc.

productivity Thursday;
and Friday
performance 7am-
and include 5pm
high- CST
performance
labels,
signs, safety
devices,
printing
systems
and
software.