


[Labels](#) / [Wire and Cable Labels](#) / [Wire and Cable Label Cards](#) /

Write-On Self-Laminating Vinyl Labels



Write-On Self-Laminating Vinyl Labels

Part Number:

SLFW-250-PK

Dimensions:

0.75 in H x 0.25 in W x 0.24 in Dia

Material:

Vinyl

Color:

Clear/White

ADD TO CART

1

[Free sample pack](#)  [Download guide](#) 

PEOPLE ALSO VIEWED

OVERVIEW

The B-292 material has good clarity outstanding water and oil resistance.

- Ideal for use in wire and cable identification
- Vinyl labels feature clear "trailer" that wraps to protect printed text
- Flexible, self-extinguishing material conforms to most surfaces
- Operating temperature of -40 to 150° F (-40 to 65.5° C)

SPECIFICATIONS

Anti-Skid Surface?	N/A
Material Number	B-292
Cards or Sheets per Pack	25
Diameter	0.24 in
Dimensions	0.75 in H x 0.25 in W x 0.24 in Dia
UOM	Pack of 25 Cards
Finish	Matte
Indoor or Outdoor Use	Outdoor Use
Maximum Service Temperature °F	158 °F
Minimum Service Temperature °F	-40 °F
Product Number	111385
UPC	662820904175
Quantity per Card or Sheet	36
Tamper Indication Type	N/A
Thickness	0.004 in
Adhesive Type	Acrylic
Applications	Cable & Wire Marking
Color	Clear/White
Label/Media Format	Pack
Material	Vinyl
Material Properties	Flame-retardant, Self-Laminating
Resistance Properties	Chemical-Resistant, Humidity-Resistant, Oil-Resistant, Water-Resistant, Weather-Resistant
Shape	Rectangle

Solutions

[Floor Marking Guide](#)
[GHS Label Compliance](#)
[Lockout Tagout Compliance](#)
[Arc Flash Labeling Requirements](#)
[Cable and Wire Label Options](#)
[Product and Barcode Labeling](#)
[Brand Protection Solutions](#)

Services


[Lockout Tagout Services](#)
[Arc Flash Services](#)
[Confined Space Services](#)
[Visual Workplace Services](#)
[Hazcom GHS Services](#)
[Software Programming & Integration](#)
[Label Template & File Conversion](#)
[Printer Use & Training](#)
[Printer Preventative Maintenance](#)
[Toll and Custom Coating](#)
[Authentication & Tracking Services](#)

Help

[Contact Us](#)
[Knowledge Center](#)
[Printer Drivers & Firmware](#)
[Brady Software Updates](#)
[Safety Data Sheets](#)
[Technical Data Sheets](#)
[WEEE-RoHS Compliance](#)
[Product Certification](#)
[Printer Registration](#)

Resources

[Find a Distributor](#)
[Printer Selection Tool](#)
[Label Selection Tool](#)
[Digital Catalog](#)
[Request a Catalog](#)



Brady (NYSE:BRC) is a manufacturer of complete solutions that identify and protect people, products and places. Brady's products help customers increase safety, security, productivity and performance and include high-performance labels, signs, safety devices, printing systems and software.

Contact
6555 W. Good Hope Rd. Milwaukee WI 53223
Phone: 888-250-3082
Hours: 7am-6pm CST Monday - Friday

About
Corporation
Privacy Policy
Terms and Conditions
Terms of Use
ISO Certificates

Other
Brady Sites
Distributor Portal
International Sites
Safety Services & Software
Smart ID
Brand Protection



2018 Brady Worldwide, Inc.