

Active

PRODUCT DRAWING
English

3D PDF

See All Documentation

TE CONNECTIVITY (TE)

050 HOUSING FFC RCPT DR 100CL

FFC | FFC

1-88179-2
TE Internal Number: 1-88179-2

Always EU RoHS/ELV Compliant

Connector Type **Housing**

Connector Style **Receptacle**

Centerline **2.54 mm [.1 in]**

Number of Positions **50**

Number of Rows **2**

See All Features

Feedback

North America

GET SAMPLE

SAVE TO LIST

Contact us to request pricing, availability and customization options.

© 2016 TE Connectivity Ltd. family of companies. All Rights Reserved

CAD Files

3D PDF
PDF
3D

Customer View Model
2D_DXF.ZIP
English

Customer View Model
3D_IGS.ZIP
English

Customer View Model
3D_STP.ZIP
English

Product Specifications

Product Specification
Connector, Flexible Flat Conductor Cable, .100 Inch Centerline
PDF
English

Application Specification
Flexible Flat Cable (FFC) Housings With Contact Cavities On 2.54-mm [.100-in.] Centerline Spacing
PDF
English

Instruction Sheets

Instruction Sheet (U.S.)

Extraction Tools
PDF
English

Extraction Tools
TIF
English

Extraction Tool For Flexible Flat Cable (FFC)
PDF
English

Extraction Tool For Flexible Flat Cable (FFC)
TIF
English

COMPATIBLE


Products - 49 Results

View All | Compare 0/10

Relation Type

RELATIONSHIP
Contacts
Identifies Contacts compatible with a given Housing

See All Contacts



PRODUCT - CONTACTS

Connectors - FFC Contacts
FFC | FFC

RCPT CONTACT, STD PRESS, FFC - 2-487406-8
TE INTERNAL NUMBER: 2-487406-8

Active

Always EU RoHS/ELV Compliant

Centerline **2.54 mm**

Wire/Cable Type **FFC**

Contact Type **Socket**

Contact Mating Area Plating Material **Gold Flash/Palladium Nickel or Gold/Nickel**

Packaging Method **Reel**

Quick View

RELATIONSHIP
Contacts
Identifies Contacts compatible with a given Housing

See All Contacts



PRODUCT - CONTACTS

Connectors - FFC Contacts
FFC | FFC

FFC SDR TAB 100 FULL SN-PB - 487561-1
TE INTERNAL NUMBER: 487561-1

Active

Not EU RoHS or ELV Compliant

Centerline **2.54 mm**

Wire/Cable Type **FFC**

Contact Type **Pin**

Contact Mating Area Plating Material **Tin-Lead**

Packaging Method **Reel**

Quick View

RELATIONSHIP
Contacts
Identifies Contacts compatible with a given Housing

See All Contacts



PRODUCT - CONTACTS

Connectors - FFC Contacts
FFC | FFC

FFC RECP CONTACT - 88017-2
TE INTERNAL NUMBER: 88017-2

Active

Always EU RoHS/ELV Compliant

Centerline **2.54 mm**

Wire/Cable Type **Round Wire, Discrete**

Contact Type **Socket**

Contact Mating Area Plating Material **Gold Flash/Palladium Nickel or Gold/Nickel**

Packaging Method **Reel**

Quick View

Generated from partsio.com