


# SCREW TERMINALS



## THRU HOLE




### SPECIFICATIONS

Terminal: Brass, Tin Plate  
Screw: Steel, Zinc Plate  
Mounting Hole: .047 (1.2)  
Current Rating: 15 AMP

CAT. NO. 8730 (Screw Installed)

## WIRE CONTACT



### SPECIFICATIONS

Terminal: Brass, Tin Plate  
Screw: Steel, Zinc Plate  
Contact: Phosphorus Bronze, Tin Plate  
Mounting Hole: .047 (1.2)  
Current Rating: 15 AMP


CAT. NO. 8737 (Screw Installed)



## LOW PROFILE SCREW TERMINALS



6-32



### SPECIFICATIONS

Rated: 15 Amps  
Terminal: .032 (.81) Brass, Matte Tin Plate  
Screw: Combination drive, Stainless Steel

CAT. NO. 1284 (No Screw Supplied)

CAT. NO. 1298 (Screw Supplied Unassembled)


CAT. NO. 1201 (Screw Installed & Captivated)

### PRINCIPLE FEATURES

- Easy to connect using solid or stranded wire, crimp lugs or terminals
- Anti-rotation tab for use with spade terminals
- Supplied with screw installed and captivated, with screw unassembled, or without screw
- Stainless steel screw will not wick



8-32




### SPECIFICATIONS

Rated: 15 Amps  
Terminal: .064 (1.6) Brass, Matte Tin Plate  
Screw: Brass, Nickel Plate

CAT. NO. 1205 (No Screw Supplied)

CAT. NO. 1207 (Screw Supplied Unassembled)


CAT. NO. 1209 (Screw Installed)



## HEAVY DUTY SCREW TERMINALS - 30 AMP



10-32



### SPECIFICATIONS

Rated: 30 Amps  
Terminal: .062 (1.6) Brass, Matte Tin Plate  
Screw: Combination drive, Stainless Steel

CAT. NO. 1293 (No Screw Supplied)

CAT. NO. 1299 (Screw Supplied Unassembled)


CAT. NO. 1202 (Screw Installed & Captivated)

### PRINCIPLE FEATURES

- Anti-rotation tab for use with spade terminals
- Below the board notched leg, to facilitate mechanical and solder connections
- Easy to connect using solid or stranded wire, crimp lugs or terminals
- Available with screw installed, unassembled, or without screw



10-32



### SPECIFICATIONS

Rated: 30 Amps  
Terminal: .064 (1.6) Brass, Matte Tin Plate  
Screw: Steel, Nickel Plate

CAT. NO. 1206 (No Screw Supplied)

CAT. NO. 1208 (Screw Supplied Unassembled)

CAT. NO. 1223 (Screw Installed)

