Pushing Performance
Since 1945

# Han 3M Base Panel 1 Lever



Image is for illustration purposes only. Please refer to product description.

| | |
|---|---|
| Part number | 09 37 003 0301 |
| Specification | Han 3M Base Panel 1 Lever |
| HARTING eCatalogue | https://harting.com/09370030301 |

## Identification

| | |
|---|---|
| Category | Hoods / Housings |
| Series of hoods/housings | Han® M |
| Type of hood/housing | Bulkhead mounted housing |
| Description of hood/housing | Straight |

## Version

| | |
|---|---|
| Size | 3 A |
| Locking type | Single locking lever |
| Field of application | Hoods/housings for rough environments |
| Pack contents | With seal screw |

## Technical characteristics

| | |
|---|---|
| Tightening torque | 1 Nm Fixing screws M3 |
| Limiting temperature | -40 ... +125 °C |
| Note on the limiting temperature | For use as a connector according to IEC 61984. |
| Degree of protection acc. to IEC 60529 | IP44<br>IP65 With seal screw<br>IP67 With seal screw |

## Material properties

| | |
|---|---|
| Material (hood/housing) | Zinc die-cast |
| Surface (hood/housing) | Powder-coated |
| Colour (hood/housing) | RAL 9005 (jet black) |
| Material (seal) | FPM |


HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.

Pushing Performance
Since 1945

## Material properties

| | |
|---|---|
| Material (locking) | Stainless steel |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |
| California Proposition 65 substances | Yes |
| California Proposition 65 substances | Lead<br>Nickel |
| Fire protection on railway vehicles | EN 45545-2 (2020-08) + A1 (2023-10) |
| Requirement set with Hazard Levels | R1 (HL 1-3)<br>R7 (HL 1-3) |

## Specifications and approvals

| | |
|---|---|
| Approvals | CE<br>DNV GL |

## Commercial data

| | |
|---|---|
| Packaging size | 10 |
| Net weight | 35 g |
| Country of origin | Romania |
| European customs tariff number | 85389099 |
| GTIN | 5713140055179 |
| eCl@ss | 27440202 Shell for industrial connectors |
| ETIM | EC000437 |
| UNSPSC 24.0 | 39121466 |


HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.