



Part Number : [310681012](#)
Product Description : 2.54mm H-DAC 64, 4
Way Receptacle Assembly, Single Row,
Polarization C
Series Number : 31068
Status : Active
Product Category : Connector Housings



Documents & Resources

Drawings
[310681012_sd.pdf](#)
[PK-30907-737-001.pdf](#)
[PK-31301-076-001.pdf](#)

3D Models and Design Files
[310681012_stp.zip](#)

Specifications
[AS-31067-100-001.pdf](#)
[PS-31100-0001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Boric acid per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents
- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Connector Housings
Series	31068
Description	2.54mm H-DAC 64, 4 Way Receptacle Assembly, Single Row, Polarization C
Application	Automotive, Power, Wire-to-Board, Wire-to-Wire
Comments	Polarization Option C, Brown
Product Name	H-DAC 64
UPC	756054393130

Physical

Circuits (maximum)	4
Color - Resin	Brown (Carmel), White
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene, Polyester
Net Weight	1.385/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to Mating Part	Yes
Ports	1

Stackable	No
Temperature Range - Operating	-40° to +100°C

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
2.54mm H-DAC 64, 4 Way Male Housing Assembly, Single Row, Polarization C, Brown	<u>310681042</u>
2.54mm H-DAC 64, 4 Way Male Housing Assembly, Single Row, Polarization C, Brown, with Xmas Tree Attachment	<u>310681072</u>
H-DAC 64 2.54mm 4 Way Right-Angle Header Assembly, Polarization C	<u>311000042</u>
H-DAC 64 2.54mm 4 Way Vertical Header Assembly, Polarization C	<u>311010042</u>

Use with Part(s)

Description	Part Number
Use With	See Product Specification

This document was generated on Mar 06, 2025