Part Number : 1731121237
Product Description : FCT High Power Contact, Female, Right-Angle, PCB Through Hole, 0.80µm Gold Mating Plating, 5.00µm Tin Termination Plating, Split Tine, 40.0A, 12-10 AWG
Series Number : 173112
Status : Active
Product Category : D-Sub Contacts
Engineering Part Number : FMP235S104



Documents and Resources

Drawings

1731121237_sd.pdf

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Specifications

1731120008-PK-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026) SCIP:1fa6b087-3564-44b1-b239-522d7ae95192
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Downloaded from Arrow.com.

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	D-Sub Contacts
Series	173112
Description	FCT High Power Contact, Female, Right-Angle, PCB Through Hole, 0.80µm Gold Mating Plating, 5.00µm Tin Termination Plating, Split Tine, 40.0A, 12-10 AWG
Contact Type	High Power
Magnetic	Yes
Product Name	FCT Products
Type	Mixed Layout
UPC	191130973415

Electrical

Current - Maximum per Contact	40.0A

Physical

Durability (mating cycles min)	500
Gender	Female
Material - Contact	Copper Alloy

Downloaded from Arrow.com.

Material - Plating Mating	Gold over Nickel
Material - Plating Termination	Tin over Nickel
Material - Retaining Clip	Copper Alloy
Net Weight	1.900/g
Orientation	Right Angle
Packaging Type	Bag
Plating min - Mating	0.800µm
Plating min - Termination	5.000µm
Temperature Range - Operating	-55° to +155°C
Termination Style	Through Hole
Wire Size (AWG)	10, 12

Mates With / Use With

Use with Part(s)

Description	Part Number
Use With	FCT Mixed Layout Connectors

Application Tooling

Global

Description	Part Number
FCT Removal Tool for Size 8 Contacts	1731121747

Downloaded from Arrow.com.