

**SCHROFF**

Project - 0 item(s)

MY PROJECT LIST

PRODUCTS

APPLICATIONS

INDUSTRIES

NEW PRODUCTS

CONFIGURATORS

Products ▾

Search



Home > Type H-ST robust, standard



Type H-ST robust, standard

SCHROFF

Other Views

**Catalog Number: 34560-528**[Back To Product](#)

- Standard where mechanical demands are high (H-ST)
- < 28 HP not printed
- For indirect backplane mounting with insulation strip
- Al extrusion, anodised finish, conductive contact surface, with HP markings
- Mounting top and bottom

Product family:

- EuropacPRO
- CompacPRO
- RatiopacPRO
- PropacPRO

Note:

Delivery is in standard pack multiples. Pricing is per individual item

Type:

Individual Components

Individual Component Type:

Horizontal Rails & Accessories



Technical Data

Length mm	147.32
Qty	1 piece (SPQ 10)
Delivery is exclusively made in Standard Pack Quantity (SPQ)	10
Material	Aluminium extrusion
Finish	Anodised, conductive contact surfaces
Description	Horizontal rail

Delivery Comprises:

Item	Quantity	Description
1	1	Horizontal rail, Al-Profile, anodised

Select product specifications before modifying or adding to project list or requesting a quote.

Length-mm-defining

147.32

[Clear Selection](#)Quantity **Add Item to Project List +****Documents**

Shock and vibration test according to IEC 48/IEC 61587




Shock and vibration test according to Deutsche Bundesbahn standards



Seismic test

Links


Native CAD files



EMC gasket kit between horizontal rail and horizontal rail

24562-528


[Add Item to Project List](#) +



Countersunk screw, torx (M4x10), steel zinc plated, PU 100 pieces

24560-155

[Add Item to Project List](#) +



Countersunk screw, torx (M4x14), steel zinc plated, PU 100 pieces

24560-130

[Add Item to Project List](#) +

EXPLORE

[About Us](#)
[Services & Capabilities](#)
[News & Events](#)
[Newsletter Subscriptions](#)
[Strategic Partnerships](#)
[Investor Relations](#)

CONTACT

[Customer Service](#)
[Find a Sales Office or Distributor](#)
[Global Locations](#)
[Product Compliance & Certifications](#)
[Partner Login](#)

DOWNLOAD

[Download Center](#)
[Reference Projects](#)
[Videos](#)
[Product Configurators](#)
[Warranties and Terms of Sale & Procurement](#)

© 2018 nVent. All rights reserved | [Privacy Policy](#) | [Terms of Use](#) | [Cookie Policy](#) | [Imprint](#) | [Site Map](#)

Connect With Us

