







DISTANCE
OF OPEN
DOOR



- NOTES:
1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
 2. DIMENSIONS IN [] ARE METRIC.
 3. WEIGHT: SEE TABLE ON PAGE 3
 4. PART INCLUDES:
 - 1- PATCHRUNNER 2 VERTICAL MANAGER, FRONT AND REAR FINGERS
 - 2- PATCHRUNNER 2 DUAL HINGE DOOR, FOR VERTICAL CABLE MANAGER
 - 1- HARDWARE KIT
 5. CAN BE USED WITH ANY 19 OR 23 INCH EIA STANDARD RACK
 6. ALL DIMENSIONS ARE REFERENCE ONLY.

PART NUMBER		PR2VD**	
TITLE		PATCHRUNNER 2 VERTICAL CABLE MANAGER, FRONT AND REAR FINGERS AND DOORS	
ITEM REVISION NAME		CUSTOMER DRAWING	
DATASET FILE NAME		14V455LV-DC	
MATERIAL:		BACKBONE & DOOR SKIN: STEEL FINGERS, CROSSBARS, DOOR ENDS, DOOR KNOBS: ABS HINGE PINS & HINGE LATCHES: POLYCARBONATE	
DRAWING NUMBER:		14V455LV-DC	
THIRD ANGLE PROJECTION		SHT 1 OF 3	
DRAWN BY		DATE	
BJN		10-24-17	
CHK		JCO	
SCALE		NONE	
SIZE		B	

00C	4-17-18	BJN	JCO	JEFK	ADDED ** TO 96" PART NUMBERS	14V455LV-DC
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	DESCRIPTION	A=OVERALL WIDTH		B=OVERALL HEIGHT		C=OVERALL DEPTH		D=DOOR WIDTH		E=DOOR HEIGHT		F=DOOR OPENING DEPTH		MANAGER AND DOORS FULY UNPACKED WEIGHT	MANAGER AND DOORS SHIPPING WEIGHT
		INCHES	MM	INCHES	MM	INCHES	MM	INCHES	MM	INCHES	MM	INCHES	MM		
PR2VD06**	PATCHRUNNER 2 VERTICAL MANAGERS AND DOORS, 6in WIDE, 7ft TALL, FRONT AND REAR	6.00	152.4	83.88	2130.4	20.7	526.4	5.99	152.1	80.77	2051.6	4.62	117.3	48.1 LBS EACH [21.8 KG EACH]	50.1 LBS EACH [22.7 KG EACH]
PR2VD08**	PATCHRUNNER 2 VERTICAL MANAGER AND DOORS, 8in WIDE, 7ft TALL, FRONT AND REAR	8.00	203.2	83.88	2130.4	20.7	526.4	7.99	202.9	80.77	2051.5	6.60	167.7	54.59 LBS EACH [24.8 KG EACH]	56.59 LBS EACH [25.7 KG EACH]
PR2VD10**	PATCHRUNNER 2 VERTICAL MANAGER AND DOORS, 10in WIDE, 7ft TALL, FRONT AND REAR	10.00	254.0	83.88	2130.4	20.7	526.4	9.99	253.7	80.82	2052.9	8.60	218.4	61.15 LBS EACH [27.7 KG EACH]	63.15 LBS EACH [28.6 KG EACH]
PR2VD12**	PATCHRUNNER 2 VERTICAL MANAGERS AND DOORS, 12in WIDE, 7ft TALL, FRONT AND REAR	12.00	304.8	83.88	2130.4	20.7	526.4	11.99	304.5	80.81	2052.6	10.60	269.2	67.64 LBS EACH [30.7 KG EACH]	69.64 LBS EACH [31.6 KG EACH]
PR2VD0696**	PATCHRUNNER 2 VERTICAL MANAGERS AND DOORS, 6in WIDE, 8ft TALL, FRONT AND REAR	6.00	152.4	95.88	2435.2	20.7	526.4	5.99	152.1	92.77	2356.4	4.62	117.3	53.76 LBS EACH [24.4 KG EACH]	55.76 LBS EACH [25.3 KG EACH]
PR2VD0896**	PATCHRUNNER 2 VERTICAL MANAGERS AND DOORS, 8in WIDE, 8ft TALL, FRONT AND REAR	8.00	203.2	95.88	2435.2	20.7	526.4	7.99	202.9	92.77	2356.3	6.60	167.7	61.06 LBS EACH [27.7 KG EACH]	63.06 LBS EACH [28.6 KG EACH]
PR2VD1096**	PATCHRUNNER 2 VERTICAL MANAGERS AND DOORS, 10in WIDE, 8ft TALL, FRONT AND REAR	10.00	254.0	95.88	2435.2	20.7	526.4	9.99	253.7	92.82	2357.7	8.60	218.4	68.44 LBS EACH [31 KG EACH]	70.44 LBS EACH [32 KG EACH]
PR2VD1296**	PATCHRUNNER 2 VERTICAL MANAGER AND DOORS, 12in WIDE, 8ft TALL, FRONT AND REAR	12.00	304.8	95.88	2435.2	20.7	526.4	11.99	304.5	92.81	2357.4	10.60	269.2	75.74 LBS EACH [34.4 KG EACH]	77.74 LBS EACH [35.3 KG EACH]
PR2VD0679	PATCHRUNNER 2 VERTICAL MANAGER AND DOORS, 6in WIDE, 6.5ft TALL, FRONT AND REAR	6.00	152.4	78.88	2003.4	20.7	526.4	5.99	152.1	75.77	1924.6	4.62	117.3	45.6 LBS EACH [20.7 KG EACH]	47.6 LBS EACH [21.6 KG EACH]
PR2VD1279	PATCHRUNNER 2 VERTICAL MANAGER AND DOORS, 12in WIDE, 6.5ft TALL, FRONT AND REAR	12.00	304.8	78.88	2003.4	20.7	526.4	11.99	304.5	75.77	1924.6	10.60	269.2	64.12 LBS EACH [29.1 KG EACH]	66.12 LBS EACH [30 KG EACH]

**DENOTES COLOR
NONE=BLACK
WH=WHITE

00C	4-17-18	BJN	JCO	JEFK	SEE SHEET 1 FOR REVISION HISTORY	14V455LV-DC
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

PART NUMBER

PR2VD**

TITLE

PATCHRUNNER 2 VERTICAL CABLE MANAGER, FRONT AND REAR FINGERS AND DOORS

CUSTOMER DRAWING

ITEM REVISION NAME

14V455LV/00

DATASET FILE NAME

14V455LV_DC/00C

MATERIAL:

BACKBONE & DOOR SKIN: STEEL
FINGERS, CROSSBARS, DOOR ENDS, DOOR KNOBS: ABS
HINGE PINS & HINGE LATCHES: POLYCARBONATE

DRAWING NUMBER:

14V455LV-DC

THIRD ANGLE PROJECTION

DRAWN BY

DATE

CHK

SCALE

BJN

10-24-17

JCO

NONE

SIZE

B

D10100DB/17

