



## 2231368-2 Product Details

[!\[\]\(95b425611cbd2b8716a140cf67c81822\_img.jpg\) Share](#) [!\[\]\(98475352b625a273242ad989dd0cabc3\_img.jpg\) Print](#) [!\[\]\(116076dec7d8ea5879a528db6ccb1b4b\_img.jpg\) Email](#) Active

### Cable Assemblies

QSFP 25GIG 30AWG 2 METER

**2231368-2** 

TE Internal Number: 2231368-2

**Product Highlights** [View All](#)

- High Speed Cable Assembly Category
- Cable Assembly Type = Pluggable / Direct Attach
- 100 Gb/s Ethernet Application
- Assembly Type = QSFP 25G
- Length = 2.00 M

[Pricing & Availability](#) [Request Sample](#) [Add to My Part List](#) [Buy Product through Distributor](#)  Feedback[Documents](#)[Features](#)[Compliance](#)**Please Note:**

Use the Product Drawing for all design activity

**Product Type Features**

Cable Assembly Category	High Speed
Cable Assembly Type	Pluggable / Direct Attach
Assembly Type 	QSFP 25G
Color 	Black
Cable Style	Madison TurboTwin - Round Jacketed

**Industry Standards**

Flammability Rating	CL2
RoHS/ELV Compliance 	RoHS compliant, ELV compliant
Lead Free Solder Processes 	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant

**Electrical Characteristics**

Connector Impedance ( $\Omega$ )	100
Data Rate (Gb/s)	25
Impedance ( $\Omega$ )	100

**Environmental**

Halogen Free	No
--------------	----

**Dimensions**

Length (M [ft]) 	2.00 [6.56]
---	-------------

**Conditions for Usage**

Wire Size - Details	30 AWG
---------------------	--------

**Configuration Features**

Configuration	Double Ended
Number of Positions 	8 pair
Number of Signal Positions 	16

**Operation/Application**

Application 	100 Gb/s Ethernet
---	-------------------

**Product Availability**

Region	Not Specified
--------	---------------

**Other**

Brand	TE Connectivity
-------	-----------------

**Related Products**

Not quite the product you're looking for?

[Find Similar Products](#)[View Part in Product Feature Selector](#)[Check for Tooling](#)**Corporate Information**

About TE	<a href="#">Quick Links</a>
Investors	<a href="#">Distributor Inventory</a>
News Room	<a href="#">Product Cross Reference</a>
Supplier Portal	<a href="#">Documents &amp; Drawings</a>
Careers	<a href="#">Product Compliance Support Center</a>
Terms & Conditions	<a href="#">Site Map</a>
Privacy Policy	
Global Accessibility Statement	

**Customer Support**

<a href="#">Email or Chat With Us</a>
<a href="#">Find a Phone Number</a>
<a href="#">Knowledge Base</a>
<a href="#">Manage Your Account</a>

**Keep Me Informed**