

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

09-52-4094

Status:

Active

Overview:

KK® Interconnect System - Molex

Description:

3.96mm Pitch KK® Crimp Housing, Female, Friction Ramp, 9 Circuits




image - Reference only

Series

Documents:

- [3D Model](#)
- [Drawing \(PDF\)](#)
- [Product Specification PS-5239-002 \(PDF\)](#)
- [Product Specification PS-5239-003 \(PDF\)](#)
- [Product Specification PS-5239-004 \(PDF\)](#)
- [Product Specification PS-5239-005 \(PDF\)](#)
- [Product Specification PS-5239-006 \(PDF\)](#)
- [Product Specification PS-5239-007 \(PDF\)](#)
- [Product Specification PS-5239-010 \(PDF\)](#)
- [Product Specification PS-5239-011 \(PDF\)](#)
- [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Crimp Housings
Series	5239
Application	Power, Wire-to-Board
Overview	KK® Interconnect System - Molex
Product Name	KK®
UPC	800753692657

Physical

Circuits (maximum)	9
Color - Resin	Natural
Gender	Female
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	2309.000/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.96mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +105°C

Material Info

Old Part Number	5239-09
-----------------	---------

Reference - Drawing Numbers

Product Specification	PS-5239-002, PS-5239-003, PS-5239-004, PS-5239-005, PS-5239-006, PS-5239-007, PS-5239-010, PS-5239-011, RPS-5239-001
Sales Drawing	SD-5239-N

EU RoHS

ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

5239Series

Mates With

Right Angle PCB Header, 5274 5272 ,
Vertical PCB Header 5271 , 5273

Use With

5168 Cat Ear Crimp Terminals for 22-28
AWG, 5167 Cat Ear Crimp Terminals for
18-24 AWG, 2478 Crimp Terminal, 2578
Crimp Terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION