

Amphenol®RF

PRODUCTS

AMPHENOL RF PART NUMBER

531-40120

Adapter, F Type Jack to F Type Jack, 75 ohm



FIND STOCK & BUY NOW

ADD TO COMPARE

ADD TO PART LIST

PRODUCT OVERVIEW

Adapter, F Type Jack to F Type Jack, 75 ohm

Product Type	Adapters
Status	Active

DOWNLOADS

 [531-40120 Customer Drawing](#) (Size: 124 KB)

PRODUCT SPECIFICATIONS

Brand	Amphenol RF
Orientation	Straight
Impedance (Ohms)	75
Adapter Side 1	F-Type
Side 1 Gender	Jack
Adapter Side 2	F-Type
Side 2 Gender	Jack
Body Finish	Tin
Body Material	Brass
Contact Finish	Tin
Contact Material	Beryllium Copper
Insulator Material	PTFE
Max Frequency (GHz)	1
Min. Temp. (Celsius)	-65
Max. Temp. (Celsius)	165

PRODUCT COMPLIANCE


Product compliance documentation, if available is listed below:

RoHS 2 (EU)	Compliant with Exemption 6C - View Certificate
-------------	--

Additional compliance information is available in our [Product Compliance Center](#).

RELATED PRODUCTS





531-40148
Adapter, F Type Jack to F Type Plug, 75 ohm

DETAILS


[Add to Parts List](#)
[Add to Compare](#)



531-40072
Adapter, F Type Plug to F Type Jack, Right Angle, 75 ohm

DETAILS


[Add to Parts List](#)
[Add to Compare](#)



531-40008
Adapter, F Type Jack to F Type Jack, 75 ohm

DETAILS


[Add to Parts List](#)
[Add to Compare](#)



531-40047-3
F-Type Right Angle PCB Jack, Bulkhead, 75 Ohm

DETAILS

[Add to Parts List](#)
[Add to Compare](#)



531-40147
Adapter, F Type Jack to F Type Jack, 75 ohm

DETAILS

[Add to Parts List](#)
[Add to Compare](#)



531-40120
Adapter, F Type Jack to F Type Jack, 75 ohm

DETAILS

[Add to Parts List](#)
[Add to Compare](#)

FOLLOW US

NEWSLETTER

AMPHENOL RF

QUICK LINKS

CONTACT US

Copyright © 2014 Amphenol RF. All Rights Reserved.

Copyright | [Terms & Conditions](#) | [Privacy Policy](#) | [Logos](#) | [Amphenol.com](#)