



1969593-8 Product Details

[Share](#) | [Print](#) | [Email](#)


✔ Active

Economy Power Connectors

HSG,REC,FREE-HANGING,GWT,DUALROW,EP2.5

1969593-8 ✔

TE Internal Number: 1969593-8

Product Highlights [View All](#)

- Economy Power 2.5 Product Line
- Connector
- Wire-to-Wire, Wire-to-Panel
- Applies To Wire/Cable
- 8 Positions

[Pricing & Availability](#) ➤

[Request Sample](#) ➤

[Add to My Part List](#) +

[Buy Product through Distributor](#) ➤

Feedback

[Documents](#)

[Features](#)

[Compliance](#)

Please Note:

Use the Product Drawing for all design activity

Product Type Features	
Product Line	Economy Power 2.5
Product Type ?	Connector
Connector Type	Housing
Sealed	No
Mechanical Attachment	
Mating Retention Type	Latch(ing)
Electrical Characteristics	
Operating Voltage Reference	AC ▾
Operating Voltage (VAC)	250
Termination Features	
Wire/Cable Size (AWG)	22 - 26
Dimensions	
Length (X-Axis) (mm [in])	12.89 [0.507]
Width (Z-Axis) (mm [in])	10.32 [0.406]
Profile Height (Y-Axis) (mm [in])	19.97 [0.786]
Body Features	
Mating Retention	With
Contact Features	
Contact Type	Pin
Housing Features	
Centerline (mm [in]) ?	2.50 [0.098]
Connector Style	Receptacle
Housing Color	White
Housing Material	Nylon - GF
Mating Alignment	With

Configuration Features	
Number of Positions ?	8
Number of Rows	2
Industry Standards	
RoHS/ELV Compliance ?	RoHS compliant, ELV compliant
Lead Free Solder Processes ?	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant
UL Flammability Rating	UL 94V-0 ▾
Environmental	
Operating Temperature (°C [°F])	-25 - +105 [-13 - +221]
Conditions for Usage	
Applies To	Wire/Cable
Glow Wire Rating	Standard Part - Not Glow Wire
Operation/Application	
Application Use	Wire-to-Wire, Wire-to-Panel
Packaging Features	
Packaging Method	Bag/Box
Other	
Brand	TE Connectivity
Comment	Panel Mount

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

