2U UPS Replacement Battery Cartridge for Select UPS

MODEL NUMBER: **RBC24V-LCD**



Highlights

- Certified premium battery cartridge
- Pre-assembled and wired battery kit offers simple installation
- Rugged leakproof construction, maintenance free
- Wide operating temperature range

Package Includes

- Pre-assembled battery pack consisting of 2 12V batteries designed to fit select 24V rack-mount SmartPro and SmartOnline models

Description

These premium UPS replacement battery cartridges breathe new life into UPS systems suffering from expired or weak internal batteries. Each replacement battery cartridge is carefully screened and certified to meet or exceed original specifications and ships ready for installation. Reusable packaging holds expired batteries for recycling center delivery. See the UPS replacement battery web page to confirm compatibility and quantity required.
COMPATIBLE WITH SU750RTXLCD2U, SU1000RTXLCD2U, SMART750RMXL2U (LCD version only), SMART1000RM2U (LCD version only), SMX1000RT2U (LCD version only) AND OTHER MODELS RECOMMENDING THIS REPLACEMENT BATTERY CARTRIDGE.

Features

- Restores UPS runtime performance to original specifications
- Comes pre-assembled and ready for installation
- Reusable packaging holds expired batteries for recycling center delivery

Specifications

OVERVIEW	
UPC Code	037332167491
BATTERY	
DC System Voltage (VDC)	24
Included Battery Set	Contains (2) 12V 9AH sealed lead acid batteries
Typical Battery Lifespan	3 to 5 years typical, depending on UPS operating conditions
PHYSICAL	
Minimum Required Rack Depth (cm)	22.86

Downloaded from Arrow.com.

Minimum Required Rack Depth (inches)	9
Shipping Dimensions (hwd / in.)	6.00 x 7.60 x 11.60
Shipping Dimensions (hwd / cm)	15.24 x 19.30 x 29.46
Shipping Weight (lbs.)	14.75
Shipping Weight (kg)	6.69
Unit Dimensions (hwd / in.)	2.600 x 7.900 x 6.000
Unit Dimensions (hwd / cm)	6.6 x 20.1 x 15.2
Unit Weight (lbs.)	12.6
Unit Weight (kg)	5.72
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	18-month limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
https://tripplite.eaton.com

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Downloaded from Arrow.com.