




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE, TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REVISIONS		DATE	APPROVED
REV.	DESCRIPTION		
A	NEW RELEASE	25/02/07	
A1	CHANGE PLUG BOOT TO MOLDED SR	01/03/07	



LENGTH & P/N Table

LENGTH	P/N	Cable Color
3FT ±1 inch	MP-5ERJ45UNNNA-003	Gray
5FT ±2 inch	MP-5ERJ45UNNNA-005	Gray
7FT ±2 inch	MP-5ERJ45UNNNA-007	Gray
10FT ±3 inch	MP-5ERJ45UNNNA-010	Gray
14FT ±3 inch	MP-5ERJ45UNNNA-014	Gray
25FT ±4 inch	MP-5ERJ45UNNNA-025	Gray
50FT ±8 inch	MP-5ERJ45UNNNA-050	Gray
75FT ±8 inch	MP-5ERJ45UNNNA-075	Gray
100FT ±8 inch	MP-5ERJ45UNNNA-100	Gray



PIN OUT: T568B		
PLUG 1	PLUG 2	COLOR
PIN 1	PIN 1	WHITE/ORANGE
PIN 2	PIN 2	ORANGE
PIN 3	PIN 3	WHITE/GREEN
PIN 4	PIN 4	BLUE
PIN 5	PIN 5	WHITE/BLUE
PIN 6	PIN 6	GREEN
PIN 7	PIN 7	WHITE/BROWN
PIN 8	PIN 8	BROWN



UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:

DECIMALS	ANGLES
X	±X°
XX	±XX
XXX	±XXX

THIRD ANGLE PROJECTION



EAR NO.

APPROVALS

DATE

LF

CHECKED

BA

RESP ENG

MFG ENG

Amphenol Cables on Demand
20 VALLEY ST. ENDICOTT, NY 13760

ASM CBL RJ45/RJ45 CAT.5E
4PR PATCH CORDS

SIZE	DWG. NO.	REV.
A	MP-5ERJ45UNNNA-XXX	A1

QAO FILE:

SCALE SHEET OF