

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2003
© COPYRIGHT 2003 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


| LOC | DIST |
|---|---|
| A1 | - |


REVISIONS


| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|---|---|---|---|---|
| | C1 | INDEX 11 ADDED | 15JAN2009 | HA | Hoffm |







2:1









1 CONTACT CAVITY SUITABLE FOR POSITIVE MATE TAB 5.2x0.8 CONTACT PN. : 969031; 969032 AND 1740206

2 CAVITY #

3 BLANK CAVITY AT # 3

4 LOCKING HOLE TO INTERLOCK THE MATING CONNECTOR WITH THE LOCKING LANCE

5 CODING SLOT

6 POLARIZATION SLOT

7 ARTWORK LOGO AND PRODUCT #

8 MATERIAL MEETS THE REQUIREMENTS OF EN 60335 (incl. GLOW WIRE TEST 750° C, without flame)

9 CLEARANCE AND CREEPAGE DISTANCE > 3.2mm

10 NEST MARKING (EXAMPLE: NEST 1)

11 DELIVERD STATE: BULK PACKAGING IN PLASTIC BAG AND CORRUGATED SHIPPING BOX PN 973058-2

1 Kontaktkammern geeignet für POSITIVE MATE TAB 5.2x0.8 Kontakt PN. : 969031; 969032 und 1740206

2 Kammer-Nr.

3 Leerkammer an Kammer Nr.3

4 Rastfenster zur Verriegelung des Gegensteckers über den federnden Rasthaken

5 Kodierungsnut

6 Polarisierungsnut

7 Firmenlogo und Produkt-Nr.

8 Material entspricht den Anforderungen der EN 60335 (incl. GLOW WIRE TEST 750° C, ohne Flamme)

9 Luft- und Kriechstrecken > 3.2mm

10 Nestmarkierung (Beispiel: Nest 1)

11 Anlieferungszustand: Schüttgut in Beutel und Versandkarton PN 973058-2

| | | | | | | | | | |
|---|---|---|---|---|---|---|---|---|---|
| | | - | - | 0-1703058-1 | C | 7 POS. SPECIAL POSITIVE MATE TAB HOUSING | 9.926 | NATURE/ natur | 1 |
| | | - | - | PART NO | REV | DESCRIPTION | WEIGHT (g) | COLOUR | ITEM NO |
| | | - | - | REVISION OF EACH ASSY NO (WHEN BLANK, USE DWG REVISION) | | | | | |
| | | - | - | WEIGHT OF EACH ASSY NO (g) | | | | | |
| QTY REQD PER ASSY | | | | PARTS LIST | | | | | |

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DWN MAHNKE, B. 02FEB2004
CHK STREDAK, F. 09FEB2004
APVD BLEICHER, M. 11FEB2004

tyco Electronics
tyco Electronics AMP GmbH
D - 64625 Bensheim

NAME 7 POS. SPECIAL POSITIVE MATE TAB HOUSING

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±0.2 mm
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±°

PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT SEE LIST
MATERIAL PA 6 8
FINISH - -

| SIZE | CAGE CODE | DRAWING NO | RESTRICTED TO |
|---|---|---|---|
| A1 | 00779 | C-1703058 | - |

CUSTOMER DRAWING | SCALE 4:1 | SHEET 1 OF 1 | REV C1

AMP 4805 REV 31MAR2000

Downloaded from: Arrow.com.