



Part Number : [5033666011](#)

Product Description : 0.50mm Pitch Easy-On FFC/
FPC Connector, Surface Mount, Right-Angle, Bottom
Contact, 60 Circuits, Height 2.00mm (.079”), Gold (Au)
plating

Series Number : 503366

Status : Obsolete

Product Category : FFC / FPC Connectors



Documents & Resources

Specifications

[PS-503366-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	FFC / FPC Connectors
Series	503366
Description	0.50mm Pitch Easy-On FFC/FPC Connector, Surface Mount, Right-Angle, Bottom Contact, 60 Circuits, Height 2.00mm (.079"), Gold (Au) plating
Product Name	Easy-On
UPC	884982109605

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	50V

Physical

Actuator Type	Front Flip
Circuits (Loaded)	60
Color - Resin	Black
Contact Position	Bottom
Durability (mating cycles max)	20
Flammability	94V-0
Mated Height	2.00mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic

Net Weight	395.310/mg
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
PCB Locator	No
PCB Mounting	Surface Mount
PCB Retention	Yes
Pitch - Mating Interface	0.50mm
Pitch - Termination Interface	0.50mm
Plating min - Mating	0.102µm
Plating min - Termination	1.016µm
Polarized to PCB	No
Stackable	No
Temperature Range - Operating	-20° to +85°C
Wire/Cable Type	FFC/FPC

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	Molex FFC – FPC connectors - Be sure to match like plating. Visit www.molex.com/product/ffc

This document was generated on Sep 22, 2025