

Product data sheet

Specifications



APC NetShelter CX, 24U, Soundproof Server Rack Enclosure, 100V to 120V, Black, 1275H x 750W x 1130D mm

AR4024X429

⚠ Discontinued

⚠ Discontinued on: Jan 15, 2024

Overview

Presentation	Specialized enclosures with integrated cooling, noise dampening, and power distribution for server and network applications in office environments.
Lead time	Special Order - Call for Quoted Lead Times

Main

Product or Component Type	Rack enclosure
Main Input Voltage	115 V 120 V
Main Output Voltage	100 V 120 V
Input Connection Type	NEMA 5-15P
output connection type	12 NEMA 5-15R
Number of rack unit	24U
Provided equipment	Casters Installation guide Key(s) Leveling feet Rack Power Distribution Unit (PDU) Side Panels

Physical

Height	50.20 in (127.5 cm)
Width	29.53 in (75 cm)
Depth	44.49 in (113 cm)
Product Weight	340.6 lb(US) (154.5 kg)
Color	Black
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	34.65 in (88.01 cm)
minimum mounting depth	28.35 in (72.01 cm)
Rack Width	19"
Permanent permissible load	1771 lb(US) (803.3 kg) static

Input

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Input Frequency	50/60 Hz
-----------------	----------

Conformance

Product Certifications	TAA compliance
Standards	EIA-310D

Ordering and shipping details

GTIN	731304298175
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	58.66 in (149 cm)
Package 1 Width	47.24 in (120 cm)
Package 1 Length	31.50 in (80 cm)
Package 1 Weight	400.6 lb(US) (181.7 kg)

Contractual warranty

Warranty	2 year (manufacturer's defect)
----------	--------------------------------



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better



Materials and Substances

[EU RoHS Directive](#)

Pro-active compliance (Product out of EU RoHS legal scope)