

Part Number : [08520123](#)

Product Description : KK 254 Crimp Terminal 6459,
30-22 AWG, Bag, Phosphor Bronze Tin (Sn)

Series Number : 6459

Status : Active

Product Category : Crimp Terminals

Engineering Part Number : 6459-(P909)L

Packaging Alternative : [08520101](#) (Reel)



Documents and Resources

Drawings

[008520123_sd.pdf](#)

[PK-2759-001-001.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)


Specifications

[PS-10-07-001.pdf](#)

[TS-10-07-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	6459
Description	KK 254 Crimp Terminal 6459, 30-22 AWG, Bag, Phosphor Bronze Tin (Sn)
Application	Wire-to-Board
Product Name	KK 254
UPC	800754225885

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.070/g
Packaging Type	Bag
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.57mm max.
Wire Size (AWG)	22, 24, 26, 28, 30

Wire Size mm ²	N/A
---------------------------	-----

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Use with Part(s)

Description	Part Number
KK 254 Single Row Crimp Housings	<u>2695</u>

Application Tooling

Global

Description	Part Number
Extraction Tool for KK 2.54mm Terminals, 30-22 AWG	<u>11030022</u>
PremiumGrade Hand Crimp Tool for KK 2.54mm Crimp Terminals, 30-22 AWG	<u>638118200</u>
Insertion Tool for KK 2.54mm Terminals, 30-22 AWG	<u>638120000</u>

This document was generated on May 20, 2026