
Downloaded from Arrow.com.


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
T70P	.052 LB (23.7 g)
OF70P	

C E

NOTES:
1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
B 2. THE T70P FACEPLATE CAN BE USED WITH PANDUIT SURFACE RACEWAY SYSTEMS AND BOXES THAT ACCEPT 70mm SNAP-ON FACEPLATES (INCLUDES: T-70, TWIN-70, TE70, TG-70, ETC.)
3. THE T70P FACEPLATE FITS NEMA STANDARD DUPLEX RECEPTACLES.
4. DIMENSIONS IN PARENTHESES ARE IN METRIC.
D 5. THE OF70P FACEPLATE CAN BE USED WITH PANDUIT OFFICE FURNITURE CORNER RACEWAY (OFCR70) AND DESK MOUNT BOX (OFR20DMB.)



REV	DATE	BY	CHK	DESCRIPTION	ECN	CHK	CUST	SUP
-	--------	---	--	E. REVISED PART WEIGHT: WAS PER 10 PCS	--------	----	----	
3	06-11-04	JBN	PM	D. ADDED NOTE #5 C. ADDED PART NUMBER OF70P	36572-15	RGRO	RGRO	
2	03-13-00	JHNU	HIW	B. REV'D NOTE 2: ADDED TG-70	36572-15	HIW	HIW	
1	06-30-99	DW	HIW	A. REVISED TITLE NAME.	36572-15	HIW	HIW	
R	02-16-98	DW	HIW	RELEASED TO PRODUCTION.	36572-15	HIW	HIW	

CAD FILENAME/LAYERS: D36572B0_DC_T70P_02A.prt

PANDUIT CORP. TINLEY PARK, ILLINOIS

T-70 SNAP-ON CLASSIC SERIES
"106"/DUPLEX FACEPLATE (T70P & OF70P)
A CUSTOMER DRAWING C

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
(.X) ± (.XXX) ±
(.XX) ±.03(.8) ANGLES ±

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY: DW
DATE: 02-16-98
CHECKED BY: HIW
MAT'L: PVC
SCALE: NONE
DRAWING NO.: 36572-15
DWG SIZE: A