**Part Number :** 1301530137
**Product Description :** Safeway In-Line Commercial GFCI, Permanent Mount, Single Phase, Manual Reset, Outlet Box, NEMA 5-20 Double Duplex, 20A, 120V, 0.61m (2.0') Cord Length
**Series Number :** 130153
**Status :** Not Recommended For New Design
**Product Category :** Power Distribution
**Engineering Part Number :** 20053-2



## Documents and Resources

### Drawings

1301530137_sd.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| China RoHS | Not Reviewed |
| EU ELV | Not Reviewed |
| Low-Halogen Status | Not Reviewed |
| REACH SVHC | Not Reviewed |
| EU RoHS | Not Reviewed |

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Downloaded from Arrow.com.

## Part Details

### General

| | |
|---|---|
| Status | Not Recommended For New Design |
| Category | Power Distribution |
| Series | 130153 |
| Description | Safeway In-Line Commercial GFCI, Permanent Mount, Single Phase, Manual Reset, Outlet Box, NEMA 5-20 Double Duplex, 20A, 120V, 0.61m (2.0') Cord Length |
| Enclosure Rating | NEMA 4 |
| NEMA Configuration | NEMA 5-20 |
| Product Name | Safeway |
| Type | GFCI Commercial Duty, Single Phase |
| UPC | 78678828423 |

### Agency

| | |
|---|---|
| CSA | LR6837 |
| UL | E66308 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 20.0A |
| GFCI | Yes-In-line |
| GFCI Reset | Manual |
| Ground Continuity Monitor | No |
| Open Neutral Relay | Yes |
| Voltage - Maximum | 240V |

### Physical

| | |
|---|---|
| Cord Diameter | 10.92mm (.430") |
| Cord Grip Body Size | Internal Double C-Clamp |
| Cord Length | 0.61m (2.0') |
| Cord Type | 12/3 SJTW |
| Feed-Thru | Yes |

Downloaded from Arrow.com.

| | |
|---|---|
| Flip Lid | No |
| Material - Housing | Nylon |
| Mounting Style | Portable |
| Number of Receptacles | 2 |
| Packaging Type | Bag |
| Receptacle Type | Duplex |

This document was generated on Sep 29, 2026

Downloaded from Arrow.com.