



Jun.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


	△数 COUNT	訂正事項 DESCRIPTION OF REVISIONS	擔當 BY	檢圖 CHKD	年月日 DATE		△数 COUNT	訂正事項 DESCRIPTION OF REVISIONS	擔當 BY	檢圖 CHKD	年月日 DATE
1	–	Revised Drawing	HMY	LHJ	18. 04. 09	4	2	EC-(RE-2-2059)	KYG	LHJ	22. 12. 12
2	2	Revised Drawing	PYB	LHJ	21. 07. 21	△					. .
3	3	Revised Drawing	KYG	LHJ	22. 01. 28	△					. .


















ISO-VIEW



[NOTE]
1. FINISH : SEE TABLE
2. CO-PLANARITY : 0.08 MAX BEFORE/AFTER REFLOW 2TIMES
3. UNSPECIFIED TOLERANCE : ±0.2
4. Lot marking : 6 digits (HYMDDL)
(H : Hirose, Y : Year, M : Month, DD : Day, L : Line)

NO.	DESCRIPTIONS	MATERIAL	1 FINISH	REMARKS
8	POTTING	SILICONE	BLACK COLOR	-
7	BOTTOM SHELL	STAINLESS STEEL	Ni1.0μm MIN	-
6	TOP SHELL	STAINLESS STEEL	Ni1.0μm MIN	-
5	INNER SHELL	STAINLESS STEEL	Cleansing	-
4	CONTACT 2nd	COPPER ALLOY	Contact Area : Au0.05μm MIN OVER Pd-Ni0.75μm MIN OVER Ni2.0μm MIN	-
3	CONTACT 1st		Solder Tails : Au0.05μm MIN OVER Ni2.0μm MIN	-
2	MID PLATE	STAINLESS STEEL	Ni1.0μm MIN	-
1	HOUSING	THERMOPLASTIC	BLACK COLOR	-

CODE NO. (OLD)	DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
	S.H.LIM 18.02.19	C.E.LIM 18.02.19	H.J.LEE 18.02.19	T.S.KANG 18.02.19	ENG 22.12.12 DEPT

SCALE 5:1 UNITS mm	DRAWING NO. EDC3-632534	PART NO. CX90MWD2-24P
	HRS HIROSE KOREA CO.,LTD.	CODE NO CL 6240-0016-6


HRS DRAWING FOR REFERENCE

Downloaded from Arrow.com.


Jun.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

DRAWING FOR PACKING


DIRECTION OF UNREELING




B-B




Detail A






A-A




PIN NUMBER




A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
GND	TX1+	TX1-	Vbus	CC1	D+	D-	SBU1	Vbus	RX2-	RX2+	GND
GND	RX1+	RX1-	Vbus	SBU2	D-	D+	CC2	Vbus	TX2-	TX2+	GND
B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1

RECOMMENDED DIMENSIONS OF THE DEVICE CHASSIS




WITH O-RING



HRS DRAWING FOR REFERENCE

[Note]

5. CARRIER TAPE PACKING



6 PEELING FORCE : 10~132 gf @ 300mm/min

7 PACKING QUANTITY
- 1,500EA / REEL
- 15,000EA / BOX (10 REEL / BOX)

NO.	DESCRIPTIONS	MATERIAL	FINISH	REMARKS
11	REEL BOBBIN	PS	White Color	-
10	COVER TAPE	PET	White Transparent Color	-
9	EMBOSS TAPE	PS	Thermo-Comperssion Sealing	-

SCALE 5:1 UNITS mm	DRAWING NO. EDC3-632534	PART NO. CX90MWD2-24P
	HRS HIROSE KOREA CO.,LTD.	CODE NO CL 6240-0016-6 2/2

Downloaded from Arrow.com.