

SmartRack 1U Blanking Panel Kit - Toolless Mounting, 10 Panels, Black

MODEL NUMBER: SR1UPANEL10



Fills unused rack spaces to help improve cooling efficiency and optimize airflow throughout.

Features

Prevents Recirculating Hot Air from Harming Your Rack-Mounted Equipment

This SmartRack® blanking panel kit is ideal for filling in unused rack spaces in your EIA-standard 19-inch rack enclosure. SR1UPANEL10 blanking panels close off unused rack openings, which improves cooling efficiency by optimizing airflow and preventing hot air from recirculating through your expensive equipment. Efficient cooling reduces operating costs, improves performance and helps your network equipment last longer.

Easy to Install with No Tools Needed

Each blanking panel's rear tabs snap easily into the front mounting rails of your rack enclosure. No tools are needed. Each blanking panel occupies 1U of rack space. Ten blanking panels are included.

Specifications

OVERVIEW	
UPC Code	037332142085
Accessory Type	Pass-Through Panel
Accessory Class	Rack Accessories
COOLING	
Cooling Type	Passive
PHYSICAL	
Shipping Dimensions (hwd / in.)	4.60 x 9.50 x 18.80
Shipping Dimensions (hwd / cm)	11.68 x 24.13 x 47.75
Shipping Weight (lbs.)	3.20

Highlights

- Helps prevent hot air from recirculating through expensive network equipment
- Optimizes airflow to improve cooling efficiency throughout the rack cabinet
- Easy to mount in 1U of rack space with no tools needed
- Compatible with EIA-standard 19-inch rack enclosures, including SmartRack cabinets

System Requirements

Compatible with all square-hole EIA-compliant rack cabinets

Package Includes

- (10) 1U blanking panels
- Installation instructions



Powering Business Worldwide

TRIPP LITE
SERIES

Shipping Weight (kg)	1.45
Unit Dimensions (hwd / in.)	1.752 x 19.000 x 1.252
Unit Dimensions (hwd / cm)	4.45 x 48.26 x 3.18
Unit Weight (lbs.)	.09
Unit Weight (kg)	0.04
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.