

har-flex THR str m 1.75mm 68p PL1 220pcs

Spotted an error? |  [Print page](#) [Back](#) 



Image is for illustration purposes only.
Please refer to product description.

- [Identification](#)[Version](#)[Technical characteristics](#)[Material properties](#)

Part number	15 11 068 2401 000
Description	har-flex THR str m 1.75mm 68p PL1 220pcs
Typblad	 PDF
Datablad	 PDF

Identification

Category	Connector
Series	har-flex®
Element	Male connector
Description of the contact	Straight
Termination method	THR connection

 [Top](#)

Version

Connection type	PCB to PCB PCB to cable
Number of contacts	68
Performance level	1
Pack contents	220 pieces on reel

 [Top](#)

Technical characteristics

Contact rows	2
Contact spacing (mating side)	1.27 mm
Stacking height	1.75 mm
Clearance distance	≥ 0.4 mm
Creepage distance	≥ 0.4 mm
Insulation resistance	> 10 ⁹ Ω
Contact resistance	< 25 mΩ
Limiting temperature	-55 ... +125 °C
Test voltage U _{r.m.s.}	0.5 kV
CTI	= 175
Flammability acc. to UL 94	V-0

 [Top](#)

Material properties

Material (insert)	LCP
Material (contacts)	Copper alloy
Surface (contacts)	Tin plated Termination side Au over Pd/Ni Mating side

[Login to MyHARTING](#)
for pricing and stock check

Quantity:

[Shopping cart](#) 

[Email inquiry](#) 

Need assistance?



Customer service

Your HARTING customer
service representative:

866-278-0306
[customerservice-
usa@harting.com](mailto:customerservice-usa@harting.com)

Catalogue

Selection Guide for Mezzanine
Applications - Page



 [Browse](#)

 [Download](#)

Downloads

Title	Downloads
Typblad	 PDF
Datablad	 PDF
Typblad	 CGM
Typblad	 DXF
CAD-data 3D	 STEP
CAD-data 3D	 JT

Recently viewed

There are no current visited product detail pages.

Recently searched

No searches have been done yet.



[Home](#) | [Contact](#) | [Privacy Policy](#) | [Terms of Use](#) | [Sales and delivery conditions](#) | [Imprint](#)

HARTING contact: HARTING Inc. of N.America | Bowes Road 1370 | 60123-5538 Elgin | USA
HARTING support: 866-278-0306 | [✉ E-mail address](#) (For questions regarding products, orders and user accounts)
Website support: +49 5772 47-9399 | [✉ E-mail address](#) (For technical problems regarding the website)

Follow us on

